



CONTROL COMPARTMENT DOOR IS NOT SHOWN IN THE DRAWING FOR SHOWING INTERNAL COMPONENTS IN CONTROL COMPARTMENT

CONTROL COMPARTMENT TERMINAL

GROUND TERMINAL

REFER NOTE 3





NOTE:
 1. BACK CHANNEL COOLING: BACK IN BACK OUT
 2. CABLE FEED: BOTTOM ENTRY & BOTTOM OUT
 3. PLINTH HEIGHT CAN BE OF 100, 200, & 400mm HEIGHT.

INTERNAL INTERFACE CABLES ARE HIDDEN IN THE DRAWING FOR BETTER CLARITY

CRITICAL CHARACTERISTICS
 KEY CHARACTERISTICS
 INSPECTION
 MUST COMPLY TO ROHS DIRECTIVE 2011/65/EU

PDM CONTROLLED DRAWING NOT VALID WITHOUT FROZEN DATE IN ID STAMP		THIRD ANGLE PROJECTION	SCALE 0.150	SIZE A1	MATERIAL
INTERPRET DIM. & TOL. PER ASME Y14.5M-1994 ALL DIMENSIONS ARE IN MILLIMETERS TOLERANCES UNLESS OTHERWISE SPECIFIED ±1.0 ±0.50 ±1.0					
DESIGNED	SABARISH MAY-21-2019			MCAD-PLV-D10H-IP54-WO OPTIONS	
CHECKED	LARI MAY-07-2019				
CONFIDENTIAL - PROPERTY OF DANFOSS A/S HØRSHØJ, DENMARK. NOT TO BE HANDED OVER TO BE COPIED OR BE USED BY A THIRD PARTY. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.				REV 002	SHEET 1 OF 3





REVISION NUMBER	REV
132R0290	002
132R0290	3 OF 3