








▽ CRITICAL CHARACTERISTICS
 ▽ KEY CHARACTERISTICS
 ○ INSPECTION
 MUST COMPLY TO ROHS DIRECTIVE 2011/65/EU

NOTE:
 1. BACK CHANNEL COOLING: BOTTOM IN TOP OUT
 2. CABLE FEED: TOP ENTRY & TOP EXIT
 3. PLINTH HEIGHT CAN BE OF 100, 200, & 400mm HEIGHT

INTERPRET DIM. & TOL. PER ASME Y14.5M-1994		THIRD ANGLE PROJECTION	SCALE	SIZE	MATERIAL
ALL DIMENSIONS ARE IN MILLIMETERS			0.125	A1	
TOLERANCES UNLESS OTHERWISE SPECIFIED					FINISH
.3±1.0 .4±0.50 ±1.0					DESCRIPTION
Danfoss					
MCAD-PLV-D9H-IP54-LHDP-DIS-TOPENTRY-EXIT					
DESIGNED	SABARISH	05/10/19			
CHECKED					
CONFIDENTIAL - PROPERTY OF DANFOSS A/S NORBORG, DENMARK. NOT TO BE HANDED OVER TO BE COPIED OR BE USED BY A THIRD PARTY. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.				DRAWING NUMBER	REV
				132R0302	001
				132R0302	1 OF 4

INPUT OPTIONS & CONTROL COMPARTMENTS VIEW





NOTE:
1. INTERNAL CABLE CONNECTIONS ARE NOT SHOWN.

