



NOTE:
 1. BACK CHANNEL COOLING: BOTTOM IN TOP OUT
 2. CABLE FEED: BOTTOM ENTRY & BOTTOM OUT
 3. PLINTH HEIGHT CAN BE OF 100, 200, & 400mm HEIGHT

▽ CRITICAL CHARACTERISTICS
 ▽ KEY CHARACTERISTICS
 ○ INSPECTION
 MUST COMPLY TO ROHS DIRECTIVE 2011/65/EU

INTERPRET DIM. & TOL. PER ASME Y14.5M-1994 ALL DIMENSIONS ARE IN MILLIMETERS TOLERANCES UNLESS OTHERWISE SPECIFIED XX±0.20 ≤ ±1.0		THIRD ANGLE PROJECTION	SCALE 0.125	SIZE A1	MATERIAL
PDM CONTROLLED DRAWING NOT VALID WITHOUT FROZEN DATE IN ID STAMP				DESCRIPTION MCAD-PLV-E5H-IP54-LHDP-CM/DVDT	
DESIGNED SABARISH	CHECKED 05/13/19			DATE 05/13/19	REV 001
CONFIDENTIAL - PROPERTY OF DANFOSS A/S NORBORG, DENMARK. NOT TO BE HANDED OVER TO BE COPIED OR BE USED BY A THIRD PARTY. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.					DRAWING NUMBER 132r0303 WORK NUMBER 132r0303

INPUT OPTIONS & CONTROL COMPARTEMENTS VIEW





