


INTERNAL INTERFACE CABLES ARE HIDDEN
IN THE DRAWING FOR BETTER CLARITY

CONTROL COMPARTMENT DOOR
IS NOT SHOWN IN THE DRAWING
FOR SHOWING INTERNAL COMPONENTS
IN CONTROL COMPARTMENT UNIT
ONLY CONTROL COMPARTMENT UNIT
IS SHOWN FOR BETTER CLARITY



2156.0 [84.88]
2000.0 [78.74]

CONTACTOR

MAINS INPUT
(SWITCH DISCONNECTOR)

DC - TERMINALS

MOTOR TERMINALS

GROUND TERMINAL

SEE DETAIL A
MAINS TERMINAL

NOTE:
1. BACK CHANNEL COOLING: BOTTOM IN TOP OUT
2. CABLE FEED: BOTTOM ENTRY & BOTTOM OUT
3. PLINTH HEIGHT CAN BE OF 100, 200, & 400mm HEIGHT

REFER NOTE 3

CRITICAL CHARACTERISTICS
KEY CHARACTERISTICS
INSPECTION
MUST COMPLY TO ROHS DIRECTIVE 2011/65/EU

INTERPRET DIM. & TOL. PER ASME Y14.5M-1994		THIRD ANGLE PROJECTION	SCALE	SIZE	MATERIAL
ALL DIMENSIONS ARE IN MILLIMETERS TOLERANCES UNLESS OTHERWISE SPECIFIED ±0.10 ±0.50 ±1.0			0.150	A1	
NOT VALID WITHOUT FROZEN DATE IN ID STAMP					FINISH
					DESCRIPTION
					MCAD-PLV-E6H-IP54-FUS-SWI-DIS+CON
CHANGED	SABARISH	MAY-29-19			
DESIGNED	Loufi	OCT-17-18			
CHECKED					
CONFIDENTIAL - PROPERTY OF DANFOSS A/S NORBORG, DENMARK. NOT TO BE HANDED OVER TO BE COPIED OR BE USED BY A THIRD PARTY. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.					REVISION
					132R0282
					REV 002
					SHEET 1 OF 3

