

TopTherm fan-and-filter units – SK 3244.100

created : 04.06.2013 on www.rittal.com/com-en



Produkt-Beschreibung

Colour: RAL 7035

Protection category to IEC 60 529: IP 54
With hose-proof hood: IP 56
With fine filter mat or hose-proof hood: IP 55

Supply includes: Unit ready for installation

Note: For energy-efficient operation of the fan-and-filter units, we recommend using enclosure internal thermostats, speed controls or digital thermostats with display.

Packs of: 1 pc.

EAN: 4028177652163

Customs tariff number: 84145100





Produkt-Merkmale

Air throughput (unimpeded air flow): At 50 Hz: 700 m³/h
At 60 Hz: 770 m³/h




Air throughput with outlet filter including standard filter mat: Number of outlet filters: 1
2
Model No. of outlet filter :
SK 3243.200
SK 3243.200
At 50 Hz: 544 m³/h
630 m³/h
At 60 Hz: 610 m³/h
690 m³/h

| | |
|-----------------------------------|--|
| Rated operating voltage: | 230 V AC/1~/50 Hz 230 V AC/1~/60 Hz |
| Dimensions: | Width: 323 mm Height: 323 mm |
| Required mounting cut-out: | Width: 292 mm Height: 292 mm |
| Build depth: | 25 mm |
| Installation depth: | 130.5 mm |
| Temperature ranges: | Bearing: - 30 °C/+ 70 °C Operation (environment): - 30 °C - + 55 °C |
| Power consumption Pel: | At 50 Hz: 95 W At 60 Hz: 135 W |
| Rated current (max.): | At 50 Hz: 0.43 A At 60 Hz: 0.6 A |
| Pre-fuse: | Miniature circuit-breaker/fuse: 4 A |
| Noise level: | At 50 Hz: 65 dB(A) At 60 Hz: 66 dB(A) |
| Diagonal fan: | Diagonal, 1~ capacitor motor |

Approbationen

| | |
|---------------------|--|
| Certificates | Sorry, there is currently no information available |
| Declarations | Sorry, there is currently no information available |
| Approvals |  CSA (EN)  UR (EN)  C-UR (EN)  Approval overview (DE) |

Downloads

| | |
|------------------------------|--|
| Documentation |  Instructions (EN) |
| Characteristic curves | Sorry, there is currently no information available |
| Videos | Sorry, there is currently no information available |
| Data sheets |  Technical System Catalogue (DE)  Performance diagrams (DE) |