

X5

X1 Mains 50mm<sup>2</sup>(5Nm)

X2 Drive 50mm<sup>2</sup>(5Nm)

X3/X4 Capacitor disconnect 16mm<sup>2</sup>(3,5Nm)

A/B Temperature 2,5mm<sup>2</sup>(0,8Nm)

597,5 ± 2,5 mm [23,5 ± 0,098 in]

336,3 ± 2,5 mm [13,2 ± 0,098 in]

PE M8

63,8 ± 2,5 mm [2,5 ± 0,098 in]

210,5 ± 1 mm [8,3 ± 0,039 in]

240,0 ± 1 mm [9,4 ± 0,039 in]

210,5 ± 1 mm [8,3 ± 0,039 in]

370,0 ± 2,5 mm [14,6 ± 0,098 in]

418,0 ± 2,5 mm [16,5 ± 0,098 in]



393,0 ± 2,5 mm [15,5 ± 0,098 in]

9,0 ± 1 mm [0,4 ± 0,039 in]

9,0 ± 1 mm [0,4 ± 0,039 in]

685,0 ± 2,5 mm [27,0 ± 0,098 in]

753,2 ± 2,5 mm [29,7 ± 0,098 in]



				DATE	Name	Designation	
				Drawn 03.03.2014	CM	X5 IP20 with external fan 1	
				Reviewed 21.08.2014	MK		
				Standard DIN 2768-1 V			
				Scale drawing 1:1		Drawing Number	
				Print scale Approx. 1:5		X5 C IP20 ef1	
R	Terminals	14.03.16	1			1	
R	Dimensions	04.07.14	1			A2	
Status	Modifications	DATE	Name			P:\14_P&D\10_Entwicklung\10_30 CAD_Baufreizezeichnungen\10_30_Breite\10_30_Überschwingfilter\GehäuseX5	