

X6

X1 Mains 70mm<sup>2</sup>(10Nm)

X2 Drive 70mm<sup>2</sup>(10Nm)

X3/X4 Capacitor disconnect 35mm<sup>2</sup>(4Nm)

A/B Temperature 2,5mm<sup>2</sup>(0,8Nm)

597,0 ± 2,5 mm [23,5 ± 0,098 in]

405,3 ± 2,5 mm [16,0 ± 0,098 in]

370,0 ± 2,5 mm [14,6 ± 0,098 in]

418,0 ± 2,5 mm [16,5 ± 0,098 in]

PE M8


94,3 ± 2,5 mm [3,7 ± 0,098 in]

210,5 ± 1,0 mm [8,3 ± 0,039 in]

240,0 ± 1,0 mm [9,4 ± 0,039 in]

210,5 ± 1,0 mm [8,3 ± 0,039 in]

393,0 ± 2,5 mm [15,5 ± 0,098 in]




9,0 ± 1,0 mm [0,4 ± 0,039 in]

9,0 ± 1,0 mm [0,4 ± 0,039 in]

685,0 ± 2,5 mm [27,0 ± 0,098 in]

767,3 ± 2,5 mm [30,2 ± 0,098 in]



|        |               |          |                     |              |  |  |    |
|--------|---------------|----------|---------------------|--------------|--|--|----|
|        |               |          |                     |              |  |  |    |
|        |               |          | DATE                | Name         | Designation  |  |    |
|        |               |          | Drawn 20.02.2014    | FR           | X6 IP20 with internal fan 2  |  |    |
|        |               |          | Reviewed 26.08.2014 | MK           |  |  |    |
|        |               |          | Standard            | DIN 2768-1 V |  |  |    |
|        |               |          | Scale drawing       | 1:1          |  |  |    |
|        |               |          | Print scale         | Approx. 1:5  | Drawing Number   |  |    |
| R      | Terminals     | 14.03.16 | 1                   |              | X6 C IP20 if2  |  | 1  |
| R      | Dimensions    | 04.07.14 | 1                   |              |  |  | A2 |
| Status | Modifications | DATE     |                     | Name         | P:\18_P8D\102_Entwicklung\03_30 CAD_Baufreizeichnungen\03_Bereitete\03_Uberschwingungsfilter\GehäuseX6 |  |    |