







Basic Unit Main Informations

Type	Value
Max Weight	10.5 kg / 22 lb
IP Class	IP20
Nema Class	Type 20



DETAIL A
SCALE 1:2



SCALE 1:20

THIS DRAWING SHOW THE MOST COMMON VERSION OF THIS VARIANT.
SMALL DIFFERENCES CAN OCCUR DEPENDING ON YOUR FINAL CONFIGURATIONS.

● CENTER OF GRAVITY:
REFERENCE ONLY, CONFIGURATIONS MAY SHIFT CG IN ALL THREE AXES

UNLESS OTHERWISE SPECIFIED TOLERANCE IS ±1mm (0.4 INCH) ALL DIMENSIONS ARE IN MILLIMETERS (INCH)		FIRST ANGLE PROJECTION	SCALE 1:10	SIZE A2	MATERIAL
					FINISH DESCRIPTION
CHANGED					f2.drw
DESIGNED	-	2013-11-21			
CHECKED					
CONFIDENTIAL: PROPERTY OF DANFOSS A/S NORDBORG, DENMARK. NOT TO BE HANDED OVER TO BE COPIED OR BE USED BY A THIRD PARTY. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.					DRAWING NUMBER F2
					MODEL 3D_F2_FRAME_STP
					REV 1 OF 2

Connetions	Max Cabel size	AWG Size
Mains	50 mm ²	22
Motor	40 mm ²	24
Control	30 mm ²	26

