







Type	Value
Max Weight	54.9 kg/120.8 lb
IP Class	IP21
Nema Class	Type 1




MOUNTING BASE




SCALE 1:10



DETAIL A  
SCALE 1:1



DETAIL B  
SCALE 1:1



THIS DRAWING SHOWS THE MOST COMMON VERSION OF THIS PRODUCT VARIANT. SMALL DIFFERENCES MAY OCCUR DEPENDING ON THE FINAL PRODUCT CONFIGURATION.

CENTER OF GRAVITY: FOR REFERENCE ONLY, THE PRODUCT CONFIGURATION MAY INFLUENCE THE CG IN ALL THREE AXES.

UNLESS OTHERWISE SPECIFIED THE TOLERANCE IS ± 1MM (0.4 INCH). ALL DIMENSIONS ARE IN MILLIMETERS (INCH).		FIRST ANGLE PROJECTION	SCALE 1:5	DRAWING SIZE A1	MATERIAL FINISH
CHANGED					
DESIGNED	DANFOSS	26-04-16			
CHECKED					
PROPERTY OF DANFOSS A/S NORDBORG, DENMARK. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.					DESCRIPTION MCAD C4 IP21 DRAWING NUMBER MCAD-C4-IP21 MODEL MCAD-C4-IP21 REV 001 SHEET 1 OF 1