




TERMINAL LOCATION  
LEFT SIDE VIEW



TERMINAL LOCATION  
FRONT VIEW



TERMINAL LOCATION  
RIGHT SIDE VIEW




LOAD SHARE LOCATION		
DIM	F1/F2	F3/F4
A	380.5 [14.98]	29.4 [1.16]
B	432.5 [17.03]	81.4 [3.20]

FRAME F1 AND F2  
IP21/IP54/UL AND NEMA1/NEMA12

⊙ CRITICAL CHARACTERISTICS  
▽ KEY CHARACTERISTICS  
○ INSPECTION  
MUST COMPLY TO ROHS DIRECTIVE 2011/65/EU

INTERPRET DIM. & TOL. PER ASME Y14.5M-1994 ALL DIMENSIONS ARE IN MILLIMETERS TOLERANCES UNLESS OTHERWISE SPECIFIED ±0.10 ±0.50 ±1.0		THIRD ANGLE PROJECTION	SCALE 0.250	SIZE A1	MATERIAL	
— PDM CONTROLLED DRAWING — NOT VALID WITHOUT FROZEN DATE IN ID STAMP				FINISH		
CHANGED	BC			05/04/18	DESCRIPTION	
DESIGNED	JM			06/14/07	DWG. REF. TERMINAL RECTIFIER CAB. F1/F2	
CHECKED			CONFIDENTIAL - PROPERTY OF DANFOSS A/S NORBORG, DENMARK. NOT TO BE HANDED OVER TO BE COPIED OR BE USED BY A THIRD PARTY. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.	TERMINAL NUMBER 177R0034	REV 204 1 OF 2	
			CABINET-RECTIFIER-PILOT			



F1/F2 LOADSHARE LOCATION

F3/F4 LOADSHARE LOCATION

