



MAINS INPUT




BOTTOM VIEW OF OUTPUT TERMINAL




CONTROL COMPARTMENT DOOR IS NOT SHOWN IN THE DRAWING FOR SHOWING INTERNAL COMPONENTS IN CONTROL COMPARTMENT

CONTROL COMPARTMENT TERMINAL



GROUND TERMINALS



4X DETAIL B SCALE 0.750

CRITICAL CHARACTERISTICS
KEY CHARACTERISTICS
INSPECTION
MUST COMPLY TO ROHS DIRECTIVE 2011/65/EU

NOTE:
1. BACK CHANNEL COOLING: BOTTOM IN TOP OUT
2. CABLE FEED: BOTTOM ENTRY & BOTTOM OUT
3. PLINTH HEIGHT CAN BE OF 100, 200, & 400mm HEIGHT.

INTERNAL INTERFACE CABLES ARE HIDDEN IN THE DRAWING FOR BETTER CLARITY

INTERPRET DIM. & TOL. PER ASME Y14.5M-1994 ALL DIMENSIONS ARE IN MILLIMETERS TOLERANCES UNLESS OTHERWISE SPECIFIED ±0.10 ±0.50 ±1.0		THIRD ANGLE PROJECTION	SCALE 0.150	SIZE A1	MATERIAL
PDM CONTROLLED DRAWING NOT VALID WITHOUT FROZEN DATE IN ID STAMP				FINISH	
CHANGED	SABARISH	MAY-21-2019		DESCRIPTION	MCAD-PLV-D10H-IP54 -CONTACTOR-DUOT-CM
DESIGNED	LAURI	MAY-07-2019			
CHECKED					
CONFIDENTIAL - PROPERTY OF DANFOSS A/S NORBORG, DENMARK. NOT TO BE HANDED OVER TO BE COPIED OR BE USED BY A THIRD PARTY. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.					DRAWING NUMBER: 132R0183 REV: 002 SHEET: 1 OF 3

