



NOTE:
 1. BACK CHANNEL: BOTTOM IN TOP OUT
 2. CABLE FEED: BOTTOM ENTRY & TOP OUT
 3. PLINTH HEIGHT CAN BE 100,200,400mm HEIGHT

⊕ CRITICAL CHARACTERISTICS
 ▽ KEY CHARACTERISTICS
 ○ INSPECTION
 MUST COMPLY TO ROHS DIRECTIVE 2011/65/EU

INTERPRET DIM. & TOL. PER ASME Y14.5M-1994 ALL DIMENSIONS ARE IN MILLIMETERS TOLERANCES UNLESS OTHERWISE SPECIFIED ±0.10 ±0.50 ±1.0		THIRD ANGLE PROJECTION	SCALE 0.150	SIZE A1	MATERIAL
— PDM CONTROLLED DRAWING — NOT VALID WITHOUT FROZEN DATE IN ID STAMP				FINISH	
CHANGED	SABARISH			MAY-21-19	DESCRIPTION
DESIGNED	Louvi	FEB-08-19	MCAD-PLV-ESH-IP54 -DISCON-CON-DVDT		
CHECKED			CONFIDENTIAL: PROPERTY OF DANFOSS A/S NORBORG, DENMARK. NOT TO BE HANDED OVER TO BE COPIED OR BE USED BY A THIRD PARTY. TWO OR THREE DIMENSIONAL REPRODUCTION OF CONTENTS TO BE AUTHORIZED BY DANFOSS A/S.		
DRAWING NUMBER 132R0271		REV 002		SHEET 1 OF 3	



