


## □ Mechanical Build-up Installation



### Follow these steps:

1. Remove the LCP (F) or Blind Cover
2. Remove the Terminal Cover (G)
3. Remove the Cable Decoupling Plate (H) and the plastic cover underneath
4. Insert the 24 V DC Back-up External Supply Option (D) in the Option Slot (E)
5. Mount the Cable Decoupling Plate (H)
6. Attach the Terminal Cover (G) and the LCP (F) or Blind Cover.

— FC 300 24 V External Supply Instruction —

□ **External 24 V DC Supply**

You can use the external 24 V DC supply as low-voltage supply to the control card or any option card installed. This enables full operation of the LCP (including the parameter setting) without connection to mains.

**External 24 V DC supply specification**

Input voltage range: 24 V DC  $\pm 15\%$   
(max. 37 V in 10 s)

Max. input current: 2.2 A

Max. cable length: 75 m

Input capacitance  $\leq 110\ \mu\text{F}$   
load:


Power-up delay:  $\leq 0.6\ \text{s}$

□ **24 V Back-Up Option**

Terminal numbers:

Terminal 35: - external 24 V DC supply.

Terminal 36: + external 24 V DC supply.



Connection to 24 V back-up supplier.