



中国船级社  
CHINA CLASSIFICATION SOCIETY

证书编号/Certificate No.  
SW20PTA00002\_01

型式认可证书  
CERTIFICATE OF TYPE APPROVAL

兹证明本证书所述制造厂具备按照下列标准的要求生产本证书所列产品的能力和条件。

This is to certify that the manufacturer stated in the certificate meets the requirements of the standards listed below and is available with the ability and conditions to produce the products described in the certificate.

制造厂/Manufacturer

VACON LTD

地址/Address

Runsorintie 7, FI-65380 Vaasa, Finland

产品名称/Product

变频器  
Frequency Converter

附加标志/Notations

无/Nil.

认可标准/Approval Standard

- 1. 中国船级社《钢质海船入级规范》（2018）及其修改通报第4篇第2、3章  
Chapter2,□3, Part Four of China Classification Society Rules for Classification of Sea-Going Steel Ships 2018 and its Amendments
- 2. 中国船级社《钢质海船入级规范》（2018）及其修改通报第7篇第2章  
Chapter2,Part Seven of China Classification Society Rules for Classification of Sea-Going Steel Ships 2018 and its Amendments

用于/Intended for

船舶与海上设施/Ships and Offshore Installations

产品明细/Product Description

变频器/Frequency Converter (M0001)

名称/Name	属性(值)/Value	单位/Unit
型号/Type	NXS, NXP, NXA, NXB (Brake-chopper unit), NXN, NXI (Inverter unit)	
功率/Power	0.55~5300	kw
频率/Frequency	Input: 45~66 Hz    Output: 0~320 Hz	
冷却方式/Cooling Method	Air-cooled or Liquid cooled	

证书有效期至/ This Certificate is valid until 2024年06月14日/ Jun. 14,2024

发证机构/ Issued by 中国船级社斯德哥尔摩办事处  
CCS Stockholm Office

签发日期/ Date 2020年07月06日  
Jul. 06,2020

本证书根据中国船级社规范及相关规定签发。所有证书页为一个整体，必须同时使用。纸质证书每页均须由本社盖章方为有效，电子证书含数字签名方为有效，本证书复印件无效。任何单位和个人均不应摘录或节选本证书的部分内容。有关方对所持证书的真实性有疑问时，可以向本社检验机构咨询。This Certificate is issued pursuant to the Rules of the Society and related regulation. All pages of the certificate are taken as a whole and are used simultaneously. No paper certificate page is valid without bearing the stamp of the Society, no electronic certificates is valid without the digital signature, and no copied form of the certificate is regarded as valid. Any part of the certificate is not to be extracted or abridged by any unit or individual in any form. Related parties who are doubted about the authenticity of the certificate may inquire of the Society or its offices.



Form No: Q01.

联系方式/Contact Us, 见本社官方网站/See official web site of the Society (<http://www.ccs.org.cn>)

UTN:P020-48850520

外壳防护等级/Degree of Protection of Enclosure	IP00, IP21, IP54	
额定输入电压/Rated Input Voltage	AC 208-690 V, DC 465-1100 V(applicable for NXI)	
额定输出电压/Rated Output Voltage	0~Uin V	

**变频器/Frequency Converter (M0002)**

名称/Name	属性(值)/Value	单位/Unit
型号/Type	Vacon 100	
功率/Power	0.55~800	kw
频率/Frequency	Input: 50/60Hz, output 0-320Hz	
冷却方式/Cooling Method	40 - 50 ° C derate 1.5% /° C, 50 - 55 ° C derate 2,5% /° C	
外壳防护等级/Degree of Protection of Enclosure	IP00, IP21, IP54	
额定输入电压/Rated Input Voltage	AC 208-690 or AC208~240V, AC380~500V, AC525~600V, AC525-690V	V
额定输出电压/Rated Output Voltage	0~Uin V	

**批准的图纸/Approved Drawings**

图纸批准号/ Drawings Approval No. : NP16A00074, NP19PPP01572, NP20PPP02304

**产品认可试验报告/ Approval Test Report**

试验报告编号/ Test Report No. : 10347418  
 试验报告日期/ Test Report Date : 2006-08-07  
 试验单位/ Laboratory: Vacon Oy  
 试验单位地址/ Test Address: Runsorintie 7, FI-65380 Vaasa, Finland

试验报告编号/ Test Report No. : VTT-S-00992-09  
 试验报告日期/ Test Report Date : 2009-01-25  
 试验单位/ Laboratory: VTT  
 试验单位地址/ Test Address: P.O. BOX 1000, FI-02044 Espoo Finland

试验报告编号/ Test Report No. : 10368261  
 试验报告日期/ Test Report Date : 2006-09-25  
 试验单位/ Laboratory: CENTRIA  
 试验单位地址/ Test Address: PL 62, Vierimaantie 7, FI-84101 Ylivieska Finland

试验报告编号/ Test Report No. : 228338-1  
 试验报告日期/ Test Report Date : 2003-04-28  
 试验单位/ Laboratory: SGS Fimko Oy  
 试验单位地址/ Test Address: Särkiniementie 3 P.O.Box 30, FIN-00210 Helsinki Finland

试验报告编号/ Test Report No. : 234713-1  
 试验报告日期/ Test Report Date : 2004-09-23  
 试验单位/ Laboratory: SGS Fimko Oy  
 试验单位地址/ Test Address: Särkiniementie 3 P.O.Box 30, FIN-00210 Helsinki Finland

试验报告编号/ Test Report No. : 231330-1  
 试验报告日期/ Test Report Date : 2004-02-12  
 试验单位/ Laboratory: SGS Fimko Oy  
 试验单位地址/ Test Address: Särkiniementie 3 P.O.Box 30, FIN-00210 Helsinki Finland

试验报告编号/ Test Report No. : 14450026, 14451070, 14454195, 14454404  
 试验报告日期/ Test Report Date : 2016-06-02  
 试验单位/ Laboratory: Vacon Oy  
 试验单位地址/ Test Address: Runsorintie 7, FI-65380 Vaasa, Finland

试验报告编号/ Test Report No. : 295115-1-1  
 试验报告日期/ Test Report Date : 2019-01-30  
 试验单位/ Laboratory: SGS Fimko Ltd

试验单位地址/ Test Address: Särkiniementie 3 P.O.Box 30, FI-00210 Helsinki Finland

试验报告编号/ Test Report No. : VTT-S-00992-09

试验报告日期/ Test Report Date : 2009-02-13

试验单位/ Laboratory: VTT

试验单位地址/ Test Address: Technical Research Centre of Finland Jari Heikkinen

试验报告编号/ Test Report No. : 290708-1-2

试验报告日期/ Test Report Date : 2018-01-15

试验单位/ Laboratory: SGS Fimko Ltd

试验单位地址/ Test Address: Särkiniementie 3 P.O.Box 30, FI-00210 Helsinki Finland

试验报告编号/ Test Report No. : Test Reports for Marine Type Approval

试验报告日期/ Test Report Date : 2015-11-23

试验单位/ Laboratory: SGS Fimko Ltd, Vacon Oy

试验单位地址/ Test Address: SGS Fimko Ltd, Vacon Oy

### 认可后的产品检验方式/ Method of Product Inspection after Approval

认可后的产品检验由制造厂按本社批准的产品检验计划进行，本社在文件审核合格后颁发船用产品证书。

After approval, product inspection should be carried out by the Manufacturer in accordance with the product inspection scheme approved by the Society, and the Marine Product Certificate is issued by the Society upon satisfactory documents review.

### 认可保持条件/ Maintenance Requirements of Approval

1. 型式认可后，如果产品及其重要零部件的设计、所用材料或制造方法有所改变，且影响到产品的主要特性、特征；或产品的性能指标有所更改，且超过认可的范围，则有关图纸和文件应经检验机构审批。并在检验机构认为必要时，经本社检验人员见证有关试验和进行检查，其结果应能证实仍符合认可条件。

After type approval, if there are changes to the design, materials used or manufacturing method of the product and important components and such changes affect major characteristics and properties of the product, or property indexes of the product are changed and exceed the scope of approval, related drawings and documents are to be examined and approved by the concerned survey office. Where deemed necessary by the survey office, the surveyor to the Society will go to witness relevant tests and conduct inspection and the results should be able to demonstrate compliance with the approval conditions.

2. 工厂的质量管理体系应保持有效运行，并且与认可时一致。如果质量管理体系发生改变，应经原体系认证机构审核并报本社批准。

The quality management system of the factory shall be ensure effective operation, and shall be the same as the situation of approval. If there are any changes to the quality management system, auditing of the original certification organization for quality management system and the society's approval shall be obtained.

3. 认可证书有效期内，如果出现可能导致本社取消认可的情况，工厂应及时采取有效的纠正措施。

Within the validity of the approval certificate, if cases occur that may cause the Society to withdraw the approval, the manufacturer should take corrective actions in a prompt and effective manner.

4. 在认可证书有效期内，本社检验人员可在未经事先通知的情况下对工厂的产品制造过程进行审核，以验证产品的生产是否符合业经本社批准的图纸和文件。工厂应予以配合。

Within the validity of the approval certificate, the surveyor to the Society may pay unannounced audit to the manufacturing process of the product in order to confirm whether it is in compliance with the drawings and documents approved by the Society. The factory should provide an active cooperation and necessary for the surveyor.

5. 型式认可A证书获得者应接受本社每年一次的定期审核，定期审核日为认可证书期满之日对应的每一周年日，检查工作应在周年日的前后三个月内进行。

Those who have obtained the certificate of type approval A should be subject to periodical audit every year. The date of periodical audit shall be each anniversary date which corresponds to the date of expiry of the relevant certificate and the periodical audit shall be done within a time span of three months before and after the annual surveillance date.

### 备注/Remarks

本社已审核了产品厂无石棉声明，但本社的审核不免除产品厂按照合同关系向订货方保证产品无石棉的责任。

The declaration of asbestos-free submitted by manufacturer has been reviewed by the Society. However, liability of the manufacturer to guarantee the products are asbestos-free to purchaser under contract will not be exempted.

本证书由原型式认可证书 (No. SW18Q00002\_01) 变更并换新。

This certificate is modified and renewed from the previous Type Approval Certificate No. SW18Q00002\_01.

1. Alternative manufacturing site:

Name: Vacon (China) Drives Co., Ltd. Haiyan Branch

Address: Building 6-7, No.339, North Xinqiao Road, Wuyuan Street, Haiyan County, 314300, Jiaxing City, Zhejiang Province, China.

Vacon (China) Drives Co., Ltd. Haiyan Branch is only for Vacon NX family.

2. Temperature range in operation: 0 - 40 °C, For marine applications size of drive to be derated with respect to an ambient temperature of 40 °C (40 - 50 °C when derated 1,5% /°C, 50 - 55 when derated 2,5% /°C, refer to manual for details).

3. Fuses for protections against overload and short-circuit are not included.

4. For specific product description of certain type designation, please refer to user manual approved by CCS (No.NP16A00074 ,NP19PPP01572 and NP20PPP02304).

5. Air cooled is suitable for de-rating method about Vacon 100.

**中国船级社斯德哥尔摩办事处**  
**CCS Stockholm Office**