


X1 Mains 35mm²(4Nm)

X2 Drive 35mm²(4Nm)


X3/X4 Capacitor disconnect 16mm²(3,5Nm)

A/B Temperature 2,5mm²(0,8Nm)




X4

489 ± 2,5 mm [19,3 ± 0,098 in]



330 ± 2,5 mm [13,0 ± 0,098 in]




157,0 ± 1 mm [6,2 ± 0,039 in] 240,0 ± 1 mm [9,4 ± 0,039 in] 157,0 ± 1 mm [6,2 ± 0,039 in]

9,0 ± 1 mm [0,4 ± 0,039 in]

54,3 ± 2,5 mm [2,1 ± 0,098 in]

353,0 ± 2,5 mm [13,9 ± 0,098 in]

378,0 ± 2,5 mm [14,9 ± 0,098 in]



9,0 ± 1 mm [0,4 ± 0,039 in]

577,0 ± 2,5 mm [22,7 ± 0,098 in]

601,0 ± 2,5 mm [23,7 ± 0,098 in]

643,8 ± 2,5 mm [25,3 ± 0,098 in]

			DATE	Name	Designation		
		Drawn	06.03.2014	CM	X4 IP20 with external fan 1		
		Reviewed	19.08.2014	MK			
		Standard	DIN 2768-1 V				
		Scale drawing	1:1				
		Print scale	Approx. 1:5		Drawing Number		
R	Terminals	14.03.16	1		X4 C IP20 ef1		
R	Dimensions	04.07.14	1		1		
Status	Modifications	DATE	NAME		A2		