

ENGINEERING
TOMORROW

Danfoss

Selection Guide | VACON® NXP Liquid Cooled | 7.5 kW – 5.3 MW

Robust, silent and space-saving control for all drive needs in demanding applications



Up to

25%

savings in total
life cycle costs
compared to air
cooled solutions

drives.danfoss.com

VACON®



Quiet. Compact. Cool.

VACON® NXP Liquid Cooled AC drives are the ultimate in space-saving, high power density AC drives. They are well suited for locations where air-cooling is difficult, expensive or impractical such as onboard ships or in locations affected by altitude, or simply where installation space is at a premium. Their robust, modular design makes the VACON® NXP a suitable platform for all drive needs in demanding applications and are available in the power range from 7.5 to 5300 kW at 380-690 VAC supply voltages.

Power packed

As no air ducts are required, liquid cooled drives are extremely compact and suitable for a wide variety of heavy industries with harsh operating conditions such as marine & offshore, pulp & paper, renewable energy and mining & metal.

Thanks to the high degree of protection (IP54) achieved with these drives, they can be installed almost anywhere in the plant or vessel. This eliminates the load on the air-conditioning system in the electrical rooms – an important cost and space consideration in many retrofit applications. And since liquid

cooled drives do not require large cooling fans, they are also among the most silent AC drives on the market.

We are committed to providing you with the ultimate in high power density. VACON® NXP liquid cooled products have one of the best power/size ratios on the market. For example, our compact 12 pulse, 1.5MW drive includes a built-in rectifier, inverter and optional brake all in the same package, and all this can be mounted in an 800 mm wide enclosure.

Our liquid cooled range offers the ultimate in motor control, for both

induction and permanent magnet motors, gearless drive applications and paralleling solutions for high power motors.

Certification and grid expertise


Our VACON® NXP liquid cooled portfolio fulfills all relevant international standards and global requirements, including marine, safety and EMC & Harmonics approvals. VACON® NXP liquid cooled AC drives can be used in regenerative energy and smart grid applications, which ensures customers can effectively monitor and control energy use and costs.

Typical segments

- Marine and offshore
- Renewable energy

- Mining and metals
- Water and wastewater
- Energy management

- Pulp and paper
- Oil and gas
- Machine building



Saving fuel at sea

In the highly competitive marine segment, increased demand for efficiency is the main reason for using AC drives in fan, winch, propulsion, and various special applications across all vessel types, from large luxury liners and cargo ships to tugboats.

What's in it for you



Minimizes investment and operation costs



Saves floor space and infrastructure needs



Saves time and money



Compact and easy to install



Virtually silent operation



Benefits

- n Compact size and high power density
- n No large air conditioning systems needed as state-of-the-art liquid cooled AC drive design allows heat loss to be transferred to the most convenient place with no need for vast amounts of filtered air
- n Easy to adapt to various uses due to ready-to-use applications
- n Flexible and scalable system for additional I/O, fieldbus and functional safety boards with five built-in expansion slots
- n Silent operation due to eliminated need for large cooling fans

Typical applications

- n Propeller and thrusters systems
- n Compressors
- n Wind turbines
- n Extruders
- n Pumps and fans
- n Test bench systems
- n Cranes and winch systems
- n Power conversion systems
- n Production lines
- n Oil rigs
- n Crushers
- n Conveyors



The liquid way to stay cool

VACON® NXP Liquid Cooled AC drives have been pioneering for more than a decade in demanding industries with a proven track record of highly reliable products. We have successfully mitigated the common risks of leakage and reliability in our product design.

Climate considerations

When comparing cooling technology solutions, it is important to understand the effects on the infrastructure of the electrical room, and the room's requirements. Additional comparison parameters are the geographical location, relevant industry and process.

In warm climates it is extremely important to observe the amount of heat load transferred to the electrical room because of its indirect effect on electrical energy consumption.

The type-tested switchgears standard EN 60439-1 specifies that the electrical room's 24-hour average temperature

should be below +35 °C and the maximum temporary temperature cannot exceed +40 °C. As a result, the cooling system in electrical rooms is typically comprised of air conditioning chillers, which are dimensioned according to the maximum heat load, the temperature inside the electrical room and the maximum temperature outdoors. The typical electrical energy consumption of air conditioning is approx. 25-33% of the cooling power.

The higher the power, the greater the savings

In many cases liquid cooled drives are the most cost-effective option, simply due to the fact that there is no need for

additional air conditioning capacity or extra ventilation for the areas in which they are used. The related savings enable shorter payback times and the higher the power, the greater the savings potential.

The continuously growing cost of energy certainly supports a wider use of liquid cooled drives technology, and the number of installations is growing rapidly.



A driving force in wind energy

VACON® AC drives are designed to provide proven performance in demanding environments. Our drives are serving the wind energy industry globally with a combined installed capacity of almost one gigawatt.

Exclusively designed for liquid cooling

Many other liquid cooled drives on the market are based on modifications of an air cooled drive, rather than exclusively designed for the purpose. The VACON® NXP Liquid Cooled dissipates only 0.1 -0.15% of its heat losses to air.* A state-of-the-art cooling heatsink enables the cooling efficiency of the components to be higher than ever.

Cooling technology advantages

Up to **25%** savings in total life cycle costs compared to air cooled solutions

20dBA

less noise than air cooled drive



25% smaller unit can deliver the same or better performance

*400 kW, 690 VAC liquid cooled drive

A portfolio for all your needs

We provide a comprehensive range of AC drive modules and enclosed drive solutions to meet all your power and control requirements.



Extensive portfolio of liquid cooled drive modules

Significant energy savings and optimal performance can be achieved with the right configuration. Liquid cooled AC drives can be used in a multitude of combinations – from a single dedicated frequency converter to large-scale Common DC bus systems.

Dedicated frequency converter

The VACON® NXP Liquid Cooled drives are available as 6- or 12-pulse frequency converters. In addition, our largest unit, the CH74, can also be used as an 18-pulse converter. The AC drive consists of a power unit, control unit and possibly one or more input chokes.

An internal brake chopper is available as standard for our smallest unit CH3. For CH72 (only 6-pulse) and CH74, it is available as internal option while in all other sizes the brake chopper is available as an option and installed externally.

Front-end units

The front-end units convert a mains AC voltage and current into a DC voltage and current. The power is transferred from the mains to a common DC bus and, in certain cases, vice versa.

Active front-end (AFE)

The AFE unit is a bi-directional (regenerative) power converter (supply unit) for the front-end of a common liquid cooled DC bus drive line-up. An external LCL filter is used at the input. This unit is suitable for applications where a low level of mains harmonics and high power factor are required. AFE units can operate in parallel to provide increased power and/or redundancy without any drive to drive communication between the units. AFE units can also be connected to the same fieldbus with inverters, and controlled and monitored via fieldbus. Fuses, LCL filters, pre-charging rectifiers and resistors can be specified and ordered separately.

The LCL filter guarantees that harmonics are not an issue in any network. With a power factor > 0.99 and low harmonics, the supply chain

transformers, generators, etc. can be sized very accurately without reserving margins for the reactive power. This can mean a saving of 10% in supply chain investments. Likewise the payback time is faster as regenerative energy is fed back to the grid.

Non-regenerative front-end (NFE)

The NFE unit is an unidirectional (motoring) power converter for the front-end of a common DC bus drive line-up. The NFE is a device that operates as a diode bridge. A dedicated external choke is used at the input. This unit is suitable as a 6 or 12 pulse rectifying device when a normal level of harmonics is accepted and no regeneration to the mains is required. NFE units can be paralleled to increase power without any drive to drive communication between the units.





Inverter unit (INU)

The INU is a bidirectional DC-fed power inverter for the supply and control of AC motors. The INU is supplied from a common DC bus drive line-up. A charging circuit is needed in case a connection to a live DC bus is required. The DC-side charging circuit is external for inverter types.

Pre-charging resistors and switches or fuses are not included in an INU delivery and must be specified and ordered separately.


Brake chopper unit (BCU)

The BCU is a unidirectional power converter for the supply of excessive energy from a common DC bus drive line-up or big AC drive to resistors where the energy is dissipated as heat. External resistors are required. However, resistors or fuses are not included in a BCU delivery and can be specified and ordered separately.


BCU's improve a drive's dynamic performance in a regenerative operating point and protect common

DC bus voltage level from overvoltage. In some cases they also reduce the need for AFE investments.

A regenerative Common DC bus system



A non-regenerative common DC bus system





VACON® NXP Liquid Cooled Enclosed drive

The low harmonic and regenerative VACON® NXP Liquid Cooled Enclosed Drives range has been developed especially with ease of use in mind. Packed full of features, these fully standardized, compact and robust AC drives with a full power range help maximize the utilization of space while minimizing overall costs.

These enclosed drives are the ideal solution for applications and locations where space is at a premium. The sturdy cabinet makes it ideal for harsh environments. See technical ratings and dimensions on page 19 for further information.

High power density

VACON® NXP Liquid Cooled Enclosed Drive can be used with AC motors in power sizes from 800–1550 kW. However, using the patented VACON® DriveSynch control concept, four enclosed drives can be run in parallel taking the power range up to an outstanding 5 MW.

Fast installation

VACON® NXP Liquid Cooled Enclosed Drives are pre-designed and engineered. That means they're good to go as soon as you receive them. Simply connect to the cooling system and the power and motor supplies. Being liquid cooled, the product is virtually silent and you'll have greater flexibility with where to put it. You don't have to worry about leaving space for air flow, and you'll save on air-conditioning energy costs.

Packed with cool performance

The enclosed unit comes equipped with the same advantages of efficient and quiet cooling performance as the

rest of the VACON® NXP product family. When we say that this product is liquid cooled, we are talking about the entire product. The modules and also all its main components, such as LCL and dU/dt filters, are liquid cooled as standard. The reliable heat exchanger is offered as an option to provide a worry-free life cycle for the product.

You can also enjoy the same fast commissioning with the aid of the easy to use Startup Wizard. The slide-out racks provide easy access for maintenance. Leakage indicators alert the operator to any potential issues in the cooling system.



A solution for all your needs

We provide enclosed solutions to any segment and application. And while we focus on the drives, you can concentrate on your performance.

Eliminate production disturbances

Continuous energy supply is important to ensure your processes are optimized. Distortions in the energy supply, caused by the presence of harmonic currents and voltages, can trigger equipment disturbances and create energy losses. VACON® front-end drives with low harmonic technology maintain a constant energy supply and eliminate the disruption harmonics can cause to production.

Advanced monitoring

The VACON® NXP Liquid Cooled Enclosed Drive's built-in Fieldbus interface communicates effectively with your process automation system. This reduces the need for cabling and gives you increased monitoring and control of process equipment.

quickly and easily disconnects and activates the power supply as and when necessary.

Safety is a given

One of the most visible features of the enclosed product is the integrated main breaker switch. This simple on/off switch

Benefits

- n Saves floor space and infrastructure needs
- n Saves time and money in installation
- n Faster and easier servicing
- n Improves safety
- n Enhances reliability
- n Low harmonic input
- n Virtually silent operation

Key features

- n Optimized design with power range up to 5 MW
- n All standard protection components included
- n Silent design with no large cooling fans needed
- n Slide-out feature
- n Leakage detector
- n AFE technology
- n Pre-engineered solution with all-liquid-cooled design (including filters)
- n Cooling system monitoring

Multiple options

VACON® NXP control

High-performance control platform for all demanding drive applications

- n Excellent processing and calculation power
- n Supports induction and permanent magnet motors
- n Maximum utilization of control features over wide power and voltage range
- n Built-in PLC functionality
- n Integration of customer-specific functionalities

Option boards

VACON® NXP control provides exceptional modularity

- n 5 plug-in extension slots
- n Fieldbus boards
- n Encoder boards
- n IO boards
- n Easy plug-in without need to remove other components

Fieldbus options

Easy integration with plant automation systems

- n PROFIBUS DP
- n DeviceNet™
- n Modbus RTU
- n CANopen

Ethernet connectivity

Ethernet connectivity allows remote drive access for monitoring, configuring and troubleshooting

- n Modbus/TCP
- n PROFINET IO
- n EtherNet/IP™
- n EtherCAT





Functional safety and reliability

Safe Torque Off (STO)

Available for all VACON® NXP drives

- n Prevents drive from generating torque on motor shaft
- n Prevents unintentional start-ups
- n Corresponds to an uncontrolled stop
- n In accordance with stop category 0, EN60204-1

Safe Stop 1 (SS1)

Available for all VACON® NXP drives

- n Initiates motor deceleration
- n Initiates STO function after application specific time delay
- n Corresponds to an uncontrolled stop
- n In accordance with stop category 1, EN60204-1

Conformal coating

- n Conformal coated circuit boards as standard
- n Improved performance
- n Increased durability
- n Reliable protection against dust and moisture
- n Extended lifetime of drive and components

ATEX- certified thermistor input

Especially designed for motor temperature supervision

- n Stops feeding energy to motor in case of over-heating
- n Certified and compliant with the European ATEX directive 94/9/EC

Commissioning made easy

User-friendly keypad

- n Removable panel with plug-in connection
- n Graphical and text keypad with multiple language support
- n Text display multi-monitoring function
- n Parameter backup and copy function with the panel's internal memory
- n The startup wizard ensures a hassle-free set up

Software modularity

All-in-One application package

- n Seven built-in software applications

Several segment-specific and advanced applications such as:

- n System Interface
- n Marine
- n and much more

VACON® NCDrive

For setting, copying, storing, printing, monitoring and controlling parameters

Includes handy Datalogger function

- n Track failure modes & perform root cause analysis

Communicates with drive via:

- n RS232
- n Ethernet TCP/IP
- n CAN (fast multiple drive monitoring)
- n CAN@Net (remote monitoring)

Independent paralleling

Our patented independent paralleling configuration of front-end (AFE) units:

- n Offer high redundancy
- n Eliminate need for drive-to-drive communication
- n Enables automatic load sharing

Dedicated applications

Intelligent system interfaces for heavy industries

VACON® System Interface Application (SIA) provides a flexible and extensive interface for use in coordinated drives, which have an overriding control system. VACON® SIA utilizes the most advanced functions of our VACON® NXP motor control software and is suitable for demanding drive systems such as those in the pulp & paper and metal industries, processing lines as well as many other standard applications.

Benefits

- n Power extension with VACON® DriveSynch
- n Master Follower functions for torque sharing
- n Freely configurable PLC logic

Dedicated marine application

Our Marine Application provides flexibility and performance across all marine segment applications. VACON® Liquid Cooled drives bring many benefits to this segment in particular such as energy efficiency, improved process availability due to high redundancy, better process quality and control, as well as silent operation and substantially reduced emissions.

Benefits

- n Black Out prevention logic
- n Cost savings in electric propulsion system
- n State-of-the-art load sharing and load trooping

VACON® NXP Grid Converter

The VACON® NXP Grid Converter is a solution that improves energy efficiency and environmental performance in marine industry use. It enables ships to source energy from local grids on shore, allowing for the ship's main generators to be completely switched off.

Benefits


- n Reduces fuel consumption and emissions
- n Reduces noise and vibrations

High power and improved redundancy

VACON® DriveSynch is a patented control concept for running standard drives in parallel to control high-power AC motors or increase the redundancy of a system. This concept suits high power single or multiple winding motors, typically above 1 MW. High power AC drives up to 5 MW can be built using standard drive components.

Benefits

- n System redundancy is higher than in a conventional drive because each unit can run independently
- n Identical units and standard modules reduce overall costs by reducing need for spares and specialist skills in engineering, installation, commissioning and maintenance



* Fiber optic link



Liquid to liquid heat exchangers

We have a range of cooling units based on liquid-to-liquid heat exchangers (HX), which improve the availability and usability of AC drive systems. The cooling units belong to the liquid cooled VACON® NXP range and offer reliable and cost-effective cooling without ventilation concerns. The heat exchanger is a pre-designed, pre-tested and fully functional package that ensures safety and reliability.

Intelligent system interfaces for heavy industries

- n Self-supporting module rack construction
- n Cooling circuit equipped with threaded joints or flanges
- n Heavy industry, stainless steel
- n Industrial water heat exchanger, three-way-valve, pump, AC drive
- n Flow and pressure sensors
- n Stainless steel AISI piping
- n Two-way-valve
- n Heat exchanger installed inside a Rittal TS8 or VSG VEDA 5000 cabinet
- n Double pumps for marine class requirements, types 120 kW and 300 kW

Ratings and dimensions

VACON® NXP Liquid Cooled AC drives, 6-pulse and 12-pulse, mains voltage 400-500 VAC

| AC drive type 6-pulse | AC drive type 12-pulse | Drive output current | | | Motor shaft power | | Power loss c/a/T* [kW] | Chassis | Choke type 6-pulse | Choke type 12-pulse |
|--------------------------|---------------------------|-----------------------------------|-----------------------------------------|-----------------------------------------|----------------------------------------------------------------|----------------------------------------------------------------|------------------------------|----------|-----------------------|------------------------|
| | | Thermal I _{th} [A] | Rated cont. I _l [A] | Rated cont. I _h [A] | Opti- mum motor at I _{th} (400 V) [kW] | Opti- mum motor at I _{th} (500 V) [kW] | | | | |
| NXP00165A0N1SWS | | 16 | 15 | 11 | 7.5 | 11 | 0.4/0.2/0.6 | CH3 | CHK0023N6A0 | |
| NXP00225A0N1SWS | | 22 | 20 | 15 | 11 | 15 | 0.5/0.2/0.7 | CH3 | CHK0023N6A0 | |
| NXP00315A0N1SWS | | 31 | 28 | 21 | 15 | 18.5 | 0.7/0.2/0.9 | CH3 | CHK0038N6A0 | |
| NXP00385A0N1SWS | | 38 | 35 | 25 | 18.5 | 22 | 0.8/0.2/1.0 | CH3 | CHK0038N6A0 | |
| NXP00455A0N1SWS | | 45 | 41 | 30 | 22 | 30 | 1.0/0.3/1.3 | CH3 | CHK0062N6A0 | |
| NXP00615A0N1SWS | | 61 | 55 | 41 | 30 | 37 | 1.3/0.3/1.5 | CH3 | CHK0062N6A0 | |
| NXP00725A0N0SWS | | 72 | 65 | 48 | 37 | 45 | 1.2/0.3/1.5 | CH4 | CHK0087N6A0 | |
| NXP00875A0N0SWS | | 87 | 79 | 58 | 45 | 55 | 1.5/0.3/1.8 | CH4 | CHK0087N6A0 | |
| NXP01055A0N0SWS | | 105 | 95 | 70 | 55 | 75 | 1.8/0.3/2.1 | CH4 | CHK0145N6A0 | |
| NXP01405A0N0SWS | | 140 | 127 | 93 | 75 | 90 | 2.3/0.3/2.6 | CH4 | CHK0145N6A0 | |
| NXP01685A0N0SWS | | 168 | 153 | 112 | 90 | 110 | 4.0/0.4/4.4 | CH5 | CHK0261N6A0 | |
| NXP02055A0N0SWS | | 205 | 186 | 137 | 110 | 132 | 5.0/0.5/5.5 | CH5 | CHK0261N6A0 | |
| NXP02615A0N0SWS | | 261 | 237 | 174 | 132 | 160 | 6.0/0.5/6.5 | CH5 | CHK0261N6A0 | |
| NXP03005A0N0SWF | | 300 | 273 | 200 | 160 | 200 | 4.5/0.5/5.0 | CH61 | CHK0400N6A0 | |
| NXP03855A0N0SWF | | 385 | 350 | 257 | 200 | 250 | 6.0/0.5/6.5 | CH61 | CHK0400N6A0 | |
| NXP04605A0N0SWF | NXP04605A0N0TWF | 460 | 418 | 307 | 250 | 315 | 6.5/0.5/7.0 | CH72 | CHK0520N6A0 | 2 x CHK0261N6A0 |
| NXP05205A0N0SWF | NXP05205A0N0TWF | 520 | 473 | 347 | 250 | 355 | 7.5/0.6/8.1 | CH72 | CHK0520N6A0 | 2 x CHK0261N6A0 |
| NXP05905A0N0SWF | NXP05905A0N0TWF | 590 | 536 | 393 | 315 | 400 | 9.0/0.7/9.7 | CH72 | CHK0650N6A0 | 2 x CHK0400N6A0 |
| NXP06505A0N0SWF | NXP06505A0N0TWF | 650 | 591 | 433 | 355 | 450 | 10.0/0.7/10.7 | CH72 | CHK0650N6A0 | 2 x CHK0400N6A0 |
| NXP07305A0N0SWF | NXP07305A0N0TWF | 730 | 664 | 487 | 400 | 500 | 12.0/0.8/12.8 | CH72 | CHK0750N6A0 | 2 x CHK0400N6A0 |
| NXP08205A0N0SWF | | 820 | 745 | 547 | 450 | 560 | 12.5/0.8/13.3 | CH63 | CHK0820N6A0 | |
| NXP09205A0N0SWF | | 920 | 836 | 613 | 500 | 600 | 14.4/0.9/15.3 | CH63 | CHK1030N6A0 | |
| NXP10305A0N0SWF | | 1030 | 936 | 687 | 560 | 700 | 16.5/1.0/17.5 | CH63 | CHK1030N6A0 | |
| NXP11505A0N0SWF | | 1150 | 1045 | 766 | 600 | 750 | 18.5/1.2/19.7 | CH63 | CHK1150N6A0 | |
| NXP13705A0N0SWF | NXP13705A0N0TWF | 1370 | 1245 | 913 | 700 | 900 | 19.0/1.2/20.2 | CH74 | 3 x CHK0520N6A0 | 2 x CHK0750N6A0 |
| NXP16405A0N0SWF | NXP16405A0N0TWF | 1640 | 1491 | 1093 | 900 | 1100 | 24.0/1.4/25.4 | CH74 | 3 x CHK0650N6A0 | 2 x CHK0820N6A0 |
| NXP20605A0N0SWF | NXP20605A0N0TWF | 2060 | 1873 | 1373 | 1100 | 1400 | 32.5/1.8/34.3 | CH74 | 3 x CHK0750N6A0 | 2 x CHK1030N6A0 |
| NXP23005A0N0SWF | | 2300 | 2091 | 1533 | 1250 | 1500 | 36.3/2.0/38.3 | CH74 | 3 x CHK0820N6A0 | |
| NXP24705A0N0SWF | NXP24705A0N0TWF | 2470 | 2245 | 1647 | 1300 | 1600 | 38.8/2.2/41.0 | 2 x CH74 | 6 x CHK0520N6A0 | 4 x CHK0650N6A0 |
| NXP29505A0N0SWF | NXP29505A0N0TWF | 2950 | 2681 | 1967 | 1550 | 1950 | 46.3/2.6/48.9 | 2 x CH74 | 6 x CHK0520N6A0 | 4 x CHK0750N6A0 |
| NXP37105A0N0SWF | NXP37105A0N0TWF | 3710 | 3372 | 2473 | 1950 | 2450 | 58.2/3.0/61.2 | 2 x CH74 | 6 x CHK0650N6A0 | 4 x CHK1030N6A0 |
| NXP41405A0N0SWF | NXP41405A0N0TWF | 4140 | 3763 | 2760 | 2150 | 2700 | 65.0/3.6/68.6 | 2 x CH74 | 6 x CHK0750N6A0 | 4 x CHK1150N6A0 |
| 2 x NXP24705A0N0SWF | 2 x NXP24705A0N0TWF | 4700 | 4300 | 3100 | 2450 | 3050 | 73.7/4.2/77.9 | 4 x CH74 | 12 x CHK0520N6A0 | 8 x CHK0650N6A0 |
| 2 x NXP29505A0N0SWF | 2 x NXP29505A0N0TWF | 5600 | 5100 | 3700 | 2900 | 3600 | 88/5/93 | 4 x CH74 | 12 x CHK0520N6A0 | 8 x CHK0750N6A0 |
| 2 x NXP37105A0N0SWF | 2 x NXP37105A0N0TWF | 7000 | 6400 | 4700 | 3600 | 4500 | 110.6/5.7/116.3 | 4 x CH74 | 12 x CHK0650N6A0 | 8 x CHK1030N6A0 |
| 2 x NXP41405A0N0SWF | 2 x NXP41405A0N0TWF | 7900 | 7200 | 5300 | 4100 | 5150 | 123.5/6.9/130.4 | 4 x CH74 | 12 x CHK0750N6A0 | 8 x CHK1150N6A0 |

I_{th} = Thermal maximum continuous RMS current. Dimensioning can be done according to this current if the process does not require any overloadability or the process does not include any load variation or margin for overloadability.

I_l = Low overloadability current. Allows +10% load variation. 10% exceeding can be continuous.

I_h = High overloadability current. Allows +50% load variation. 50% exceeding can be continuous.

All values with cosφ = 0,83 and efficiency = 97%

*) c = power loss into coolant; a = power loss into air; T = total power loss; power losses of input chokes not included. All power losses obtained using max. supply voltage, I_{th} and switching frequency of 3.6 kHz and Closed Loop control mode. All power losses are worst case losses.

If some other mains voltage is used, apply the formula $P = \sqrt{3} \times U_n \times I_n \times \cos\phi \times \text{eff}\%$ to calculate the NX Liquid-Cooled drive output power.

The enclosure class for all NX Liquid-Cooled AC drives is IP00.

If the motor is continuously run at frequencies below 5 Hz (besides start and stop ramps), please pay attention to the drive dimensioning for low frequencies, i.e. maximum I = 0.66 * I_{th} or choose drive according to I_l. It is recommended to check the rating with your distributor or Vacon.

Drive overrating may also be necessary if the process requires high starting torque.

VACON® NXP Liquid Cooled AC drives, 6-pulse and 12-pulse, mains voltage 525-690 VAC

| AC drive type 6-pulse | AC drive type 12-pulse | Drive output current | | | Motor shaft power | | Power loss c/a/T* [kW] | Chassis | Choke type 6-pulse | Choke type 12-pulse |
|--------------------------|---------------------------|-----------------------------------|-----------------------------------------|-----------------------------------------|----------------------------------------------------------------|----------------------------------------------------------------|------------------------------|----------|-----------------------|------------------------|
| | | Thermal I _{th} [A] | Rated cont. I _L [A] | Rated cont. I _H [A] | Opti- mum motor at I _{th} (525 V) [kW] | Opti- mum motor at I _{th} (690 V) [kW] | | | | |
| NXP01706A0T0SWF | | 170 | 155 | 113 | 110 | 160 | 4.0/0.2/4.2 | CH61 | CHK0261N6A0 | |
| NXP02086A0T0SWF | | 208 | 189 | 139 | 132 | 200 | 4.8/0.3/5.1 | CH61 | CHK0261N6A0 | |
| NXP02616A0T0SWF | | 261 | 237 | 174 | 160 | 250 | 6.3/0.3/6.6 | CH61 | CHK0261N6A0 | |
| NXP03256A0T0SWF | NXP03256A0T0TWF | 325 | 295 | 217 | 200 | 300 | 7.2/0.4/7.6 | CH72 | CHK0400N6A0 | 2 x CHK0261N6A0 |
| NXP03856A0T0SWF | NXP03856A0T0TWF | 385 | 350 | 257 | 250 | 355 | 8.5/0.5/9.0 | CH72 | CHK0400N6A0 | 2 x CHK0261N6A0 |
| NXP04166A0T0SWF | NXP04166A0T0TWF | 416 | 378 | 277 | 250 | 355 | 9.1/0.5/9.6 | CH72 | CHK0520N6A0 | 2 x CHK0261N6A0 |
| NXP04606A0T0SWF | NXP04606A0T0TWF | 460 | 418 | 307 | 300 | 400 | 10.0/0.5/10.5 | CH72 | CHK0520N6A0 | 2 x CHK0261N6A0 |
| NXP05026A0T0SWF | NXP05026A0T0TWF | 502 | 456 | 335 | 355 | 450 | 11.2/0.6/11.8 | CH72 | CHK0520N6A0 | 2 x CHK0261N6A0 |
| NXP05906A0T0SWF | | 590 | 536 | 393 | 400 | 560 | 12.4/0.7/13.1 | CH63 | CHK0650N6A0 | |
| NXP06506A0T0SWF | | 650 | 591 | 433 | 450 | 600 | 14.2/0.8/15.0 | CH63 | CHK0650N6A0 | |
| NXP07506A0T0SWF | | 750 | 682 | 500 | 500 | 700 | 16.4/0.9/17.3 | CH63 | CHK0750N6A0 | |
| NXP08206A0T0SWF | NXP08206A0T0TWF | 820 | 745 | 547 | 560 | 800 | 17.3/1.0/18.3 | CH74 | 3 x CHK0400N6A0 | 2 x CHK0520N6A0 |
| NXP09206A0T0SWF | NXP09206A0T0TWF | 920 | 836 | 613 | 650 | 850 | 19.4/1.1/20.5 | CH74 | 3 x CHK0400N6A0 | 2 x CHK0520N6A0 |
| NXP10306A0T0SWF | NXP10306A0T0TWF | 1030 | 936 | 687 | 700 | 1000 | 21.6/1.2/22.8 | CH74 | 3 x CHK0400N6A0 | 2 x CHK0520N6A0 |
| NXP11806A0T0SWF | NXP11806A0T0TWF | 1180 | 1073 | 787 | 800 | 1100 | 25.0/1.3/26.3 | CH74 | 3 x CHK0400N6A0 | 2 x CHK0650N6A0 |
| NXP13006A0T0SWF | NXP13006A0T0TWF | 1300 | 1182 | 867 | 900 | 1200 | 27.3/1.5/28.8 | CH74 | 3 x CHK0520N6A0 | 2 x CHK0650N6A0 |
| NXP15006A0T0SWF | NXP15006A0T0TWF | 1500 | 1364 | 1000 | 1050 | 1400 | 32.1/1.7/33.8 | CH74 | 3 x CHK0520N6A0 | 2 x CHK0820N6A0 |
| NXP17006A0T0SWF | NXP17006A0T0TWF | 1700 | 1545 | 1133 | 1150 | 1550 | 36.5/1.9/38.4 | CH74 | 3 x CHK0650N6A0 | 2 x CHK1030N6A0 |
| NXP18506A0T0SWF | NXP18506A0T0TWF | 1850 | 1682 | 1233 | 1250 | 1650 | 39.0/2.0/41.0 | 2 x CH74 | 6 x CHK0400N6A0 | 4 x CHK0520N6A0 |
| NXP21206A0T0SWF | NXP21206A0T0TWF | 2120 | 1927 | 1413 | 1450 | 1900 | 44.9/2.4/47.3 | 2 x CH74 | 6 x CHK0400N6A0 | 4 x CHK0650N6A0 |
| NXP23406A0T0SWF | NXP23406A0T0TWF | 2340 | 2127 | 1560 | 1600 | 2100 | 49.2/2.6/51.8 | 2 x CH74 | 6 x CHK0400N6A0 | 4 x CHK0650N6A0 |
| NXP27006A0T0SWF | NXP27006A0T0TWF | 2700 | 2455 | 1800 | 1850 | 2450 | 57.7/3.1/60.8 | 2 x CH74 | 6 x CHK0520N6A0 | 4 x CHK0750N6A0 |
| NXP31006A0T0SWF | NXP31006A0T0TWF | 3100 | 2818 | 2066 | 2150 | 2800 | 65.7/3.4/69.1 | 2 x CH74 | 6 x CHK0520N6A0 | 4 x CHK0820N6A0 |
| 2 x NXP18506A0T0SWF | 2 x NXP18506A0T0TWF | 3500 | 3200 | 2300 | 2400 | 3150 | 74,2/3,8/77,9 | 4 x CH74 | 12 x CHK0400N6A0 | 8 x CHK0520N6A0 |
| 2 x NXP21206A0T0SWF | 2 x NXP21206A0T0TWF | 4000 | 3600 | 2700 | 2750 | 3600 | 85,4/4,5/89,9 | 4 x CH74 | 12 x CHK0400N6A0 | 8 x CHK0650N6A0 |
| 2 x NXP23406A0T0SWF | 2 x NXP23406A0T0TWF | 4400 | 4000 | 2900 | 3050 | 3950 | 93,4/5,0/98,4 | 4 x CH74 | 12 x CHK0400N6A0 | 8 x CHK0650N6A0 |
| 2 x NXP27006A0T0SWF | 2 x NXP27006A0T0TWF | 5100 | 4600 | 3400 | 3500 | 4600 | 109,7/5,8/115,5 | 4 x CH74 | 12 x CHK0520N6A0 | 8 x CHK0750N6A0 |
| 2 x NXP31006A0T0SWF | 2 x NXP31006A0T0TWF | 5900 | 5400 | 3900 | 4050 | 5300 | 124,8/6,5/131,3 | 4 x CH74 | 12 x CHK0520N6A0 | 8 x CHK0820N6A0 |

Standard air cooled chokes for VACON® NX Liquid Cooled product range

| Choke type | Losses to air [W] | Dimensions W x H x D [mm] | Weight [kg] |
|-------------|-------------------|---------------------------|-------------|
| CHK0023N6A0 | 145 | 230 x 179 x 121 | 10 |
| CHK0038N6A0 | 170 | 270 x 209 x 145 | 15 |
| CHK0062N6A0 | 210 | 300 x 214 x 160 | 20 |
| CHK0087N6A0 | 250 | 300 x 233 x 170 | 26 |
| CHK0145N6A0 | 380 | 200 x 292 x 185 | 37 |
| CHK0261N6A0 | 460 | 354 x 357 x 230 | 53 |
| CHK0400N6A0 | 610 | 350 x 421 x 262 | 84 |
| CHK0520N6A0 | 810 | 497 x 446 x 244 | 115 |
| CHK0650N6A0 | 890 | 497 x 496 x 244 | 130 |
| CHK0750N6A0 | 970 | 497 x 527 x 273 | 170 |
| CHK0820N6A0 | 1020 | 497 x 529 x 275 | 170 |
| CHK1030N6A0 | 1170 | 497 x 677 x 307 | 213 |
| CHK1150N6A0 | 1420 | 497 x 677 x 307 | 213 |

VACON® NXP Liquid Cooled inverter units, DC bus voltage 465-800 VDC

| AC drive type | Drive output current | | | Motor shaft power | | Power loss c/a/T* [kW] | Chassis |
|---------------------|--------------------------------|-----------------------------------|-----------------------------------|----------------------------------------------------|----------------------------------------------------|------------------------------|----------|
| | Thermal I _{th} [A] | Rated cont. I _L [A] | Rated cont. I _H [A] | Optimum motor at I _{th} (540 VDC) [kW] | Optimum motor at I _{th} (675 VDC) [kW] | | |
| NXP00165A0T1IWS | 16 | 15 | 11 | 7.5 | 11 | 0.4/0.2/0.6 | CH3 |
| NXP00225A0T1IWS | 22 | 20 | 15 | 11 | 15 | 0.5/0.2/0.7 | CH3 |
| NXP00315A0T1IWS | 31 | 28 | 21 | 15 | 18.5 | 0.7/0.2/0.9 | CH3 |
| NXP00385A0T1IWS | 38 | 35 | 25 | 18.5 | 22 | 0.8/0.2/1.0 | CH3 |
| NXP00455A0T1IWS | 45 | 41 | 30 | 22 | 30 | 1.0/0.3/1.3 | CH3 |
| NXP00615A0T1IWS | 61 | 55 | 41 | 30 | 37 | 1.3/0.3/1.5 | CH3 |
| NXP00725A0T0IWS | 72 | 65 | 48 | 37 | 45 | 1.2/0.3/1.5 | CH4 |
| NXP00875A0T0IWS | 87 | 79 | 58 | 45 | 55 | 1.5/0.3/1.8 | CH4 |
| NXP01055A0T0IWS | 105 | 95 | 70 | 55 | 75 | 1.8/0.3/2.1 | CH4 |
| NXP01405A0T0IWS | 140 | 127 | 93 | 75 | 90 | 2.3/0.3/2.6 | CH4 |
| NXP01685A0T0IWS | 168 | 153 | 112 | 90 | 110 | 2.5/0.3/2.8 | CH5 |
| NXP02055A0T0IWS | 205 | 186 | 137 | 110 | 132 | 3.0/0.4/3.4 | CH5 |
| NXP02615A0T0IWS | 261 | 237 | 174 | 132 | 160 | 4.0/0.4/4.4 | CH5 |
| NXP03005A0T0IWF | 300 | 273 | 200 | 160 | 200 | 4.5/0.4/4.9 | CH61 |
| NXP03855A0T0IWF | 385 | 350 | 257 | 200 | 250 | 5.5/0.5/6.0 | CH61 |
| NXP04605A0T0IWF | 460 | 418 | 307 | 250 | 315 | 5.5/0.5/6.0 | CH62 |
| NXP05205A0T0IWF | 520 | 473 | 347 | 250 | 355 | 6.5/0.5/7.0 | CH62 |
| NXP05905A0T0IWF | 590 | 536 | 393 | 315 | 400 | 7.5/0.6/8.1 | CH62 |
| NXP06505A0T0IWF | 650 | 591 | 433 | 355 | 450 | 8.5/0.6/9.1 | CH62 |
| NXP07305A0T0IWF | 730 | 664 | 487 | 400 | 500 | 10.0/0.7/10.7 | CH62 |
| NXP08205A0T0IWF | 820 | 745 | 547 | 450 | 560 | 12.5/0.8/13.3 | CH63 |
| NXP09205A0T0IWF | 920 | 836 | 613 | 500 | 600 | 14.4/0.9/15.3 | CH63 |
| NXP10305A0T0IWF | 1030 | 936 | 687 | 560 | 700 | 16.5/1.0/17.5 | CH63 |
| NXP11505A0T0IWF | 1150 | 1045 | 766 | 600 | 750 | 18.4/1.1/19.5 | CH63 |
| NXP13705A0T0IWF | 1370 | 1245 | 913 | 700 | 900 | 15.5/1.0/16.5 | CH64 |
| NXP16405A0T0IWF | 1640 | 1491 | 1093 | 900 | 1100 | 19.5/1.2/20.7 | CH64 |
| NXP20605A0T0IWF | 2060 | 1873 | 1373 | 1100 | 1400 | 26.5/1.5/28.0 | CH64 |
| NXP23005A0T0IWF | 2300 | 2091 | 1533 | 1250 | 1500 | 29.6/1.7/31.3 | CH64 |
| NXP24705A0T0IWF | 2470 | 2245 | 1647 | 1300 | 1600 | 36.0/2.0/38.0 | 2 x CH64 |
| NXP29505A0T0IWF | 2950 | 2681 | 1967 | 1550 | 1950 | 39.0/2.4/41.4 | 2 x CH64 |
| NXP37105A0T0IWF | 3710 | 3372 | 2473 | 1950 | 2450 | 48.0/2.7/50.7 | 2 x CH64 |
| NXP41405A0T0IWF | 4140 | 3763 | 2760 | 2150 | 2700 | 53.0/3.0/56.0 | 2 x CH64 |
| 2 x NXP24705A0T0IWF | 4700 | 4300 | 3100 | 2450 | 3050 | 69.1/3.9/73 | 4 x CH64 |
| 2 x NXP29505A0T0IWF | 5600 | 5100 | 3700 | 2900 | 3600 | 74.4/4.6/79 | 4 x CH64 |
| 2 x NXP37105A0T0IWF | 7000 | 6400 | 4700 | 3600 | 4500 | 90.8/5.2/96 | 4 x CH64 |
| 2 x NXP41405A0T0IWF | 7900 | 7200 | 5300 | 4100 | 5150 | 101.2/5.8/107 | 4 x CH64 |

The voltage classes for the inverter units used in the tables above have been defined as follows:

Input 540 VDC = Rectified 400 VAC supply

Input 675 VDC = Rectified 500 VAC supply

VACON® NXP Liquid Cooled inverter units, DC bus voltage 640-1100 VDC ¹⁾

| AC drive type | Drive output current | | | Motor shaft power | | Power loss c/a/T* [kW] | Chassis |
|---------------------|--------------------------------|-----------------------------------|-----------------------------------|----------------------------------------------------|----------------------------------------------------|------------------------------|----------|
| | Thermal I _{th} [A] | Rated cont. I _L [A] | Rated cont. I _H [A] | Optimum motor at I _{th} (710 VDC) [kW] | Optimum motor at I _{th} (930 VDC) [kW] | | |
| NXP01706A0T0IWF | 170 | 155 | 113 | 110 | 160 | 3.6/0.2/3.8 | CH61 |
| NXP02086A0T0IWF | 208 | 189 | 139 | 132 | 200 | 4.3/0.3/4.6 | CH61 |
| NXP02616A0T0IWF | 261 | 237 | 174 | 160 | 250 | 5.4/0.3/5.7 | CH61 |
| NXP03256A0T0IWF | 325 | 295 | 217 | 200 | 300 | 6.5/0.3/6.8 | CH62 |
| NXP03856A0T0IWF | 385 | 350 | 257 | 250 | 355 | 7.5/0.4/7.9 | CH62 |
| NXP04166A0T0IWF | 416 | 378 | 277 | 250 | 355 | 8.0/0.4/8.4 | CH62 |
| NXP04606A0T0IWF | 460 | 418 | 307 | 300 | 400 | 8.7/0.4/9.1 | CH62 |
| NXP05026A0T0IWF | 502 | 456 | 335 | 355 | 450 | 9.8/0.5/10.3 | CH62 |
| NXP05906A0T0IWF | 590 | 536 | 393 | 400 | 560 | 10.9/0.6/11.5 | CH63 |
| NXP06506A0T0IWF | 650 | 591 | 433 | 450 | 600 | 12.4/0.7/13.1 | CH63 |
| NXP07506A0T0IWF | 750 | 682 | 500 | 500 | 700 | 14.4/0.8/15.2 | CH63 |
| NXP08206A0T0IWF | 820 | 745 | 547 | 560 | 800 | 15.4/0.8/16.2 | CH64 |
| NXP09206A0T0IWF | 920 | 836 | 613 | 650 | 850 | 17.2/0.9/18.1 | CH64 |
| NXP10306A0T0IWF | 1030 | 936 | 687 | 700 | 1000 | 19.0/1.0/20.0 | CH64 |
| NXP11806A0T0IWF | 1180 | 1073 | 787 | 800 | 1100 | 21.0/1.1/22.1 | CH64 |
| NXP13006A0T0IWF | 1300 | 1182 | 867 | 900 | 1200 | 24.0/1.3/25.3 | CH64 |
| NXP15006A0T0IWF | 1500 | 1364 | 1000 | 1050 | 1400 | 28.0/1.5/29.5 | CH64 |
| NXP17006A0T0IWF | 1700 | 1545 | 1133 | 1150 | 1550 | 32.1/1.7/33.8 | CH64 |
| NXP18506A0T0IWF | 1850 | 1682 | 1233 | 1250 | 1650 | 34.2/1.8/36.0 | 2 x CH64 |
| NXP21206A0T0IWF | 2120 | 1927 | 1413 | 1450 | 1900 | 37.8/2.0/39.8 | 2 x CH64 |
| NXP23406A0T0IWF | 2340 | 2127 | 1560 | 1600 | 2100 | 43.2/2.3/45.5 | 2 x CH64 |
| NXP27006A0T0IWF | 2700 | 2455 | 1800 | 1850 | 2450 | 50.4/2.7/53.1 | 2 x CH64 |
| NXP31006A0T0IWF | 3100 | 2818 | 2066 | 2150 | 2800 | 57.7/3.1/60.8 | 2 x CH64 |
| 2 x NXP18506A0T0IWF | 3500 | 3200 | 2300 | 2400 | 3150 | 64,9/3,5/68,4 | 4 x CH64 |
| 2 x NXP21206A0T0IWF | 4000 | 3600 | 2700 | 2750 | 3600 | 71,8/3,8/75,6 | 4 x CH64 |
| 2 x NXP23406A0T0IWF | 4400 | 4000 | 2900 | 3050 | 3950 | 82,1/4,4/86,5 | 4 x CH64 |
| 2 x NXP27006A0T0IWF | 5100 | 4600 | 3400 | 3500 | 4600 | 95,8/5,1/100,9 | 4 x CH64 |
| 2 x NXP31006A0T0IWF | 5900 | 5400 | 3900 | 4050 | 5300 | 109,7/5,8/115,5 | 4 x CH64 |

¹⁾ High power 525-690V AFE, INU and BCU units available as wide voltage range version (NX_8 models) with DC bus voltage 640-1200 VDC. The units are ordered with the nominal mains voltage code 8 instead of 6 as for the standard version.

The following additional requirements applies to the wide voltage version:

- output filter with an inductance of at least 0.7% needed
- external 24VDC supply for the control unit

The voltage classes for the inverter units used in the tables above have been defined as follows:

Input 710 VDC = Rectified 525 VAC supply

Input 930 VDC = Rectified 690 VAC supply

VACON® NXP Liquid Cooled dimensions: drives consisting of one module

| Chassis | Width [mm] | Height [mm] | Depth [mm] | Weight [kg] |
|---------|------------|-------------|------------|-------------|
| CH3 | 160 | 431 | 246 | 15 |
| CH4 | 193 | 493 | 257 | 22 |
| CH5 | 246 | 553 | 264 | 40 |
| CH60 | 246 | 673 | 374 | 55 |
| CH61/62 | 246 | 658 | 372 | 55 |
| CH63 | 505 | 923 | 375 | 120 |
| Ch64 | 746 | 923 | 375 | 180 |
| CH72 | 246 | 1076 | 372 | 90 |
| Ch74 | 746 | 1175 | 385 | 280 |

One-module drive dimensions (mounting base included). Please note that AC chokes are not included.

VACON® NXN Liquid Cooled non regenerative front-end, DC bus voltage 465-800 V DC, 6/12-pulse

| AC drive type | AC current | | | DC power | | | | Power loss c/a/T*) [kW] | Chassis |
|---------------|--------------------------------|-----------------------------|-----------------------------|------------------------------------------|------------------------------------------|-----------------------------------------|-----------------------------------------|-------------------------------|---------|
| | Thermal I _{th} [A] | Rated I _L [A] | Rated I _H [A] | 400 VAC mains I _{th} [kW] | 500 VAC mains I _{th} [kW] | 400 VAC mains I _L [kW] | 500 VAC mains I _L [kW] | | |
| NXN20006A0T0 | 2000 | 1818 | 1333 | 1282 | 1605 | 1165 | 1458 | 5.7/0.5/6.2 | CH60 |

VACON® NXN Liquid Cooled non regenerative front-end, DC bus voltage 640-1100 V DC, 6/12-pulse

| AC drive type | AC current | | | DC power | | | | Power loss c/a/T*) [kW] | Chassis |
|---------------|--------------------------------|-----------------------------|-----------------------------|------------------------------------------|------------------------------------------|-----------------------------------------|-----------------------------------------|-------------------------------|---------|
| | Thermal I _{th} [A] | Rated I _L [A] | Rated I _H [A] | 525 VAC mains I _{th} [kW] | 690 VAC mains I _{th} [kW] | 525 VAC mains I _L [kW] | 690 VAC mains I _L [kW] | | |
| NXN20006A0T0 | 2000 | 1818 | 1333 | 1685 | 2336 | 1531 | 2014 | 5.7/0.5/6.2 | CH60 |

VACON® NXN Liquid Cooled non regenerative front-end line filters

| Choke type | Suitability | Power loss c/a/T*) [kW] | Dimensions 1 pc W x H x D | Total weight [kg] | Pcs for NXN | Cooling |
|-------------------|---------------------------|----------------------------|------------------------------|----------------------|----------------|---------|
| CHK1030N6A0 | NXN20006A0T0TWVA1A2BHB100 | 0/1.17/1.17 | 497 x 677 x 307 | 213 | 2 | Air |
| FLU-CHK-1030-6-DL | NXN20006A0T0WVVA1A2BHB100 | 1.18/0.5/1.68 | 506 x 676 x 302 | 237 | 2 | Liquid |

VACON® NXA Liquid Cooled active front-end, DC bus voltage 465-800 VDC

| AC drive type | AC current | | | DC power | | | | Power loss c/a/T*) [kW] | Chassis |
|-----------------|--------------------------------|-----------------------------|-----------------------------|------------------------------------------|------------------------------------------|-----------------------------------------|-----------------------------------------|-------------------------------|---------|
| | Thermal I _{th} [A] | Rated I _L [A] | Rated I _H [A] | 400 VAC mains I _{th} [kW] | 500 VAC mains I _{th} [kW] | 400 VAC mains I _L [kW] | 500 VAC mains I _L [kW] | | |
| NXA01685A0T02WS | 168 | 153 | 112 | 113 | 142 | 103 | 129 | 2.5/0.3/2.8 | CH5 |
| NXA02055A0T02WS | 205 | 186 | 137 | 138 | 173 | 125 | 157 | 3.0/0.4/3.4 | CH5 |
| NXA02615A0T02WS | 261 | 237 | 174 | 176 | 220 | 160 | 200 | 4.0/0.4/4.4 | CH5 |
| NXA03005A0T02WF | 300 | 273 | 200 | 202 | 253 | 184 | 230 | 4.5/0.4/4.9 | CH61 |
| NXA03855A0T02WF | 385 | 350 | 257 | 259 | 324 | 236 | 295 | 5.5/0.5/6.0 | CH61 |
| NXA04605A0T02WF | 460 | 418 | 307 | 310 | 388 | 282 | 352 | 5.5/0.5/6.0 | CH62 |
| NXA05205A0T02WF | 520 | 473 | 347 | 350 | 438 | 319 | 398 | 6.5/0.5/7.0 | CH62 |
| NXA05905A0T02WF | 590 | 536 | 393 | 398 | 497 | 361 | 452 | 7.5/0.6/8.1 | CH62 |
| NXA06505A0T02WF | 650 | 591 | 433 | 438 | 548 | 398 | 498 | 8.5/0.6/9.1 | CH62 |
| NXA07305A0T02WF | 730 | 664 | 487 | 492 | 615 | 448 | 559 | 10.0/0.7/10.7 | CH62 |
| NXA08205A0T02WF | 820 | 745 | 547 | 553 | 691 | 502 | 628 | 10.0/0.7/10.7 | CH63 |
| NXA09205A0T02WF | 920 | 836 | 613 | 620 | 775 | 563 | 704 | 12.4/0.8/12.4 | CH63 |
| NXA10305A0T02WF | 1030 | 936 | 687 | 694 | 868 | 631 | 789 | 13.5/0.9/14.4 | CH63 |
| NXA11505A0T02WF | 1150 | 1045 | 767 | 775 | 969 | 704 | 880 | 16.0/1.0/17.0 | CH63 |
| NXA13705A0T02WF | 1370 | 1245 | 913 | 923 | 1154 | 839 | 1049 | 15.5/1.0/16.5 | CH64 |
| NXA16405A0T02WF | 1640 | 1491 | 1093 | 1105 | 1382 | 1005 | 1256 | 19.5/1.2/20.7 | CH64 |
| NXA20605A0T02WF | 2060 | 1873 | 1373 | 1388 | 1736 | 1262 | 1578 | 26.5/1.5/28.0 | CH64 |
| NXA23005A0T02WF | 2300 | 2091 | 1533 | 1550 | 1938 | 1409 | 1762 | 29.6/1.7/31.3 | CH64 |

VACON® NXA Liquid Cooled active front-end, DC bus voltage 640-1100 VDC ¹⁾

| AC drive type | AC current | | | DC power | | | | Power loss c/a/T* [kW] | Chassis |
|-----------------|--------------------------------|-----------------------------|-----------------------------|------------------------------------------|------------------------------------------|-----------------------------------------|-----------------------------------------|------------------------------|---------|
| | Thermal I _{th} [A] | Rated I _L [A] | Rated I _H [A] | 525 VAC mains I _{th} [kW] | 690 VAC mains I _{th} [kW] | 525 VAC mains I _L [kW] | 690 VAC mains I _L [kW] | | |
| NXA01706A0T02WF | 170 | 155 | 113 | 150 | 198 | 137 | 180 | 3.6/0.2/3.8 | CH61 |
| NXA02086A0T02WF | 208 | 189 | 139 | 184 | 242 | 167 | 220 | 4.3/0.3/4.6 | CH61 |
| NXA02616A0T02WF | 261 | 237 | 174 | 231 | 303 | 210 | 276 | 5.4/0.3/5.7 | CH61 |
| NXA03256A0T02WF | 325 | 295 | 217 | 287 | 378 | 261 | 343 | 6.5/0.3/6.8 | CH62 |
| NXA03856A0T02WF | 385 | 350 | 257 | 341 | 448 | 310 | 407 | 7.5/0.4/7.9 | CH62 |
| NXA04166A0T02WF | 416 | 378 | 277 | 368 | 484 | 334 | 439 | 8.0/0.4/8.4 | CH62 |
| NXA04606A0T02WF | 460 | 418 | 307 | 407 | 535 | 370 | 486 | 8.7/0.4/9.1 | CH62 |
| NXA05026A0T02WF | 502 | 456 | 335 | 444 | 584 | 403 | 530 | 9.8/0.5/10.3 | CH62 |
| NXA05906A0T02WF | 590 | 536 | 393 | 522 | 686 | 474 | 623 | 10.9/0.6/11.5 | CH63 |
| NXA06506A0T02WF | 650 | 591 | 433 | 575 | 756 | 523 | 687 | 12.4/0.7/13.1 | CH63 |
| NXA07506A0T02WF | 750 | 682 | 500 | 663 | 872 | 603 | 793 | 14.4/0.8/15.2 | CH63 |
| NXA08206A0T02WF | 820 | 745 | 547 | 725 | 953 | 659 | 866 | 15.4/0.8/16.2 | CH64 |
| NXA09206A0T02WF | 920 | 836 | 613 | 814 | 1070 | 740 | 972 | 17.2/0.9/18.1 | CH64 |
| NXA10306A0T02WF | 1030 | 936 | 687 | 911 | 1197 | 828 | 1088 | 19.0/1.0/20.0 | CH64 |
| NXA11806A0T02WF | 1180 | 1073 | 787 | 1044 | 1372 | 949 | 1247 | 21.0/1.1/22.1 | CH64 |
| NXA13006A0T02WF | 1300 | 1182 | 867 | 1150 | 1511 | 1046 | 1374 | 24.0/1.3/25.3 | CH64 |
| NXA15006A0T02WF | 1500 | 1364 | 1000 | 1327 | 1744 | 1207 | 1586 | 28.0/1.5/29.5 | CH64 |
| NXA17006A0T02WF | 1700 | 1545 | 1133 | 1504 | 1976 | 1367 | 1796 | 32.1/1.7/33.8 | CH64 |

¹⁾ DC bus voltage 640-1200 VDC for wide range voltage version (NX_8).

* C = power loss into coolant, A = power loss into air, T = total power loss

VACON® Liquid Cooled regenerative line filters

| LCL filter type | Suitability | Power loss c/a/T* [kW] | Dimensions L _{net} 1 pcs WxHxD [mm] | Dimensions L _{drive} 1 pcs (total 3pcs) WxHxD [mm] | Dimensions C _{bank} 1 pcs WxHxD [mm] | Total weight [kg] |
|-----------------|----------------------------|------------------------------|----------------------------------------------------|-------------------------------------------------------------------|-----------------------------------------------------|----------------------|
| RLC-0385-6-0 | CH62/690VAC: 325A & 385A | 2,6/0,8/3,4 | 580 x 450 x 385 | 410 x 415 x 385 | 360 x 265 x 150 | 458 |
| RLC-0520-6-0 | CH62/500-690VAC | 2,65/0,65/3,3 | 580 x 450 x 385 | 410 x 415 x 385 | 360 x 265 x 150 | 481 |
| RLC-0750-6-0 | CH62/500VAC, CH63/690VAC | 3,7/1/4,7 | 580 x 450 x 385 | 410 x 450 x 385 | 360 x 275 x 335 | 508 |
| RLC-0920-6-0 | CH63/500VAC, CH64/690VAC | 4,5/1,4/5,9 | 580 x 500 x 390 | 410 x 500 x 400 | 360 x 275 x 335 | 577 |
| RLC-1180-6-0 | CH63/500VAC, CH64/690VAC | 6,35/1,95/8,3 | 585 x 545 x 385 | 410 x 545 x 385 | 350 x 290 x 460 | 625 |
| RLC-1640-6-0 | CH64/500-690VAC | 8,2/2,8/11 | 585 x 645 x 385 | 420 x 645 x 385 | 350 x 290 x 460 | 736 |
| RLC-2300-5-0 | CH64/500VAC: 2060A & 2300A | 9,5/2,9/12,4 | 585 x 820 x 370 | 410 x 820 x 380 | 580 x 290 x 405 | 896 |

The RLC filter contains a 3-phase choke on the mains side, capacitors and 3pcs 1-phase chokes on the AFE side.

VACON® NXB Liquid Cooled external brake chopper, DC bus voltage 460-800 VDC

| AC drive type | Current | | | | Braking power | | Power loss c/a/T* [kW] | Chassis |
|-----------------|-----------------------------------------------------|----------------------------------|----------------------------------|-------------------------------|--------------------------------------------|--------------------------------------------|------------------------|---------|
| | BCU rated cont. braking current I _{br} [A] | Rated min resistance 800 VDC (Ω) | Rated min resistance 600 VDC (Ω) | Rated max input current (Adc) | Rated cont. braking power 2*R 800 VDC [kW] | Rated cont. braking power 2*R 600 VDC [kW] | | |
| NXB00315A0T08WS | 2*31 | 25.7 | 19.5 | 62 | 49 | 37 | 0.7/0.2/0.9 | CH3 |
| NXB00615A0T08WS | 2*61 | 13.1 | 9.9 | 122 | 97 | 73 | 1.3/0.3/1.5 | CH3 |
| NXB00875A0T08WS | 2*87 | 9.2 | 7.0 | 174 | 138 | 105 | 1.5/0.3/1.8 | CH4 |
| NXB01055A0T08WS | 2*105 | 7.6 | 5.8 | 210 | 167 | 127 | 1.8/0.3/2.1 | CH4 |
| NXB01405A0T08WS | 2*140 | 5.7 | 4.3 | 280 | 223 | 169 | 2.3/0.3/2.6 | CH4 |
| NXB01685A0T08WS | 2*168 | 4.7 | 3.6 | 336 | 267 | 203 | 2.5/0.3/2.8 | CH5 |
| NXB02055A0T08WS | 2*205 | 3.9 | 3.0 | 410 | 326 | 248 | 3.0/0.4/3.4 | CH5 |
| NXB02615A0T08WS | 2*261 | 3.1 | 2.3 | 522 | 415 | 316 | 4.0/0.4/4.4 | CH5 |
| NXB03005A0T08WF | 2*300 | 2.7 | 2.0 | 600 | 477 | 363 | 4.5/0.4/4.9 | CH61 |
| NXB03855A0T08WF | 2*385 | 2.1 | 1.6 | 770 | 613 | 466 | 5.5/0.5/6.0 | CH61 |
| NXB04605A0T08WF | 2*460 | 1.7 | 1.3 | 920 | 732 | 556 | 5.5/0.5/6.0 | CH62 |
| NXB05205A0T08WF | 2*520 | 1.5 | 1.2 | 1040 | 828 | 629 | 6.5/0.5/7.0 | CH62 |
| NXB05905A0T08WF | 2*590 | 1.4 | 1.1 | 1180 | 939 | 714 | 7.5/0.6/8.1 | CH62 |
| NXB06505A0T08WF | 2*650 | 1.2 | 1.0 | 1300 | 1035 | 786 | 8.5/0.6/9.1 | CH62 |
| NXB07305A0T08WF | 2*730 | 1.1 | 0.9 | 1460 | 1162 | 833 | 10.0/0.7/10.7 | CH62 |

VACON® NXB Liquid Cooled external brake chopper, DC bus voltage 640-1100 VDC ¹⁾

| AC drive type | Current | | | | Braking power | | Power loss c/a/T* [kW] | Chassis |
|-----------------|-----------------------------------------------------|-----------------------------------|----------------------------------|-------------------------------|---------------------------------------------|--------------------------------------------|------------------------|---------|
| | BCU rated cont. braking current I _{br} [A] | Rated min resistance 1100 VDC (Ω) | Rated min resistance 840 VDC (Ω) | Rated max input current (Adc) | Rated cont. braking power 2*R 1100 VDC [kW] | Rated cont. braking power 2*R 840 VDC [kW] | | |
| NXB01706A0T08WF | 2*170 | 6.5 | 4.9 | 340 | 372 | 282 | 4.5/0.2/4.7 | CH61 |
| NXB02086A0T08WF | 2*208 | 5.3 | 4 | 416 | 456 | 346 | 5.5/0.3/5.8 | CH61 |
| NXB02616A0T08WF | 2*261 | 4.2 | 3.2 | 522 | 572 | 435 | 5.5/0.3/5.8 | CH61 |
| NXB03256A0T08WF | 2*325 | 3.4 | 2.6 | 650 | 713 | 542 | 6.5/0.3/6.8 | CH62 |
| NXB03856A0T08WF | 2*385 | 2.9 | 2.2 | 770 | 845 | 643 | 7.5/0.4/7.9 | CH62 |
| NXB04166A0T08WF | 2*416 | 2.6 | 2 | 832 | 913 | 693 | 8.1/0.4/8.4 | CH62 |
| NXB04606A0T08WF | 2*460 | 2.4 | 1.8 | 920 | 1010 | 767 | 8.5/0.4/8.9 | CH62 |
| NXB05026A0T08WF | 2*502 | 2.2 | 1.7 | 1004 | 1100 | 838 | 10.0/0.5/10.5 | CH62 |

¹⁾ DC bus voltage 640-1136 VDC for wide range voltage version (NX_8).

NOTE: The rated currents in given ambient (+50 °C) and coolant (+30 °C) temperatures are achieved only when the switching frequency is equal to or less than the factory default.

NOTE: Braking power: $P_{brake} = 2 * U_{brake}^2 / R_{resistor}$, when 2 resistors are used

NOTE: Max input DC current: $I_{in,max} = P_{brake,max} / U_{brake}$

VACON® NXP Liquid Cooled AC drive, internal brake chopper unit, braking voltage 460-800 VDC

| Converter Type | Loadability | Braking capacity 600 VDC | | Braking capacity 800 VDC | | Chassis |
|----------------------------|--------------------------|--------------------------------|------------------------------------------------------|--------------------------------|------------------------------------------------------|---------|
| | Rated min resistance [Ω] | Rated cont. braking power [kW] | BCU rated cont. braking current, I _{br} [A] | Rated cont. braking power [kW] | BCU rated cont. braking current, I _{br} [A] | |
| NX_460-730 5 ¹⁾ | 1.3 | 276 | 461 | 492 | 615 | CH72 |
| NX_1370-2300 5 | 1.3 | 276 | 461 | 492 | 615 | CH74 |

¹⁾ Only 6 pulse drives

VACON® NXP Liquid Cooled AC drive, internal brake chopper unit, braking voltage 840-1100 VDC

| Converter Type | Loadability | Braking capacity 840 VDC | | Braking capacity 1100 VDC | | Chassis |
|----------------------------|--------------------------|--------------------------------|------------------------------------------------------|--------------------------------|------------------------------------------------------|---------|
| | Rated min resistance [Ω] | Rated cont. braking power [kW] | BCU rated cont. braking current, I _{br} [A] | Rated cont. braking power [kW] | BCU rated cont. braking current, I _{br} [A] | |
| NX_325-502 6 ¹⁾ | 2.8 | 252 | 300 | 432 | 392 | CH72 |
| NX_820-1700 6 | 2.8 | 252 | 300 | 432 | 392 | CH74 |

¹⁾ Only 6 pulse drives

The internal brake chopper can also be used in motor application where 2...4 x Ch7x drives are used for a single motor, but in this case the DC connections of the power modules must be connected together.

VACON® external brake resistors for liquid cooled CH72 (CH74) drives – IP20

| Product code | Voltage range [VDC] | Maximum brake power [kW] | Maximum average power [kW] (1 puls/2min) | Resistance [Ω] | Maximum energy [kJ] (predefined power pulse) | Dimensions W x H x D [mm] | Weight [kg] |
|-----------------------------|---------------------|--------------------------|------------------------------------------|----------------|----------------------------------------------|---------------------------|-------------|
| BRW-0730-LD-5 ¹⁾ | 465...800 VDC | 637 ³⁾ | 13.3 | 1.3 | 1594 | 480 x 600 x 740 | 55 |
| BRW-0730-HD-5 ²⁾ | 465...800 VDC | 637 ³⁾ | 34.5 | 1.3 | 4145 | 480 x 1020 x 740 | 95 |
| BRW-0502-LD-6 ¹⁾ | 640...1100 VDC | 516 ⁴⁾ | 10.8 | 2.8 | 1290 | 480 x 760 x 530 | 40 |
| BRW-0502-HD-6 ²⁾ | 640...1100 VDC | 516 ⁴⁾ | 28 | 2.8 | 3354 | 480 x 1020 x 740 | 85 |

NOTE: Thermal protection switch included

1) LD = Light Duty: 5s nominal torque braking from nominal speed reduced linearly to zero once per 120s

2) HD = Heavy duty: 3s nominal torque braking at nominal speed + 7s nominal torque braking from nominal speed reduced linearly to zero once per 120s.

3) at 911 VDC

4) at 1200 VDC

Liquid to liquid heat exchangers

| | HXL-M/V/R-040-N-P | HXL/M-M/V/R-120-N-P | HXL/M-M/R-300-N-P |
|---------------------------------------------|-------------------------|--------------------------------------------------------------|--------------------------------------------------------------|
| Cooling power | 0...40 kW | 0...120 kW | 0...300 kW |
| Mains supply | 380...420 VAC | 380...420 VAC | 380...500 VAC |
| Flow | 40...120 l/min | 120...360 l/min | 360...900 l/min |
| Distribution pressure | 0.3 bar / l=10 m, DN32* | HXL: 1 bar / l = 40 m, DN50 HXM: 0.7 bar / l = 30 m, DN50 | HXL: 1 bar / l = 40 m, DN80 HXM: 0.7 bar / l = 25 m, DN80 |
| Double pump | | HXM | HXM |
| Cabinets | VEDA, Rittal | VEDA, Rittal | Rittal |
| Dimensions W x H x D [mm] (without cabinet) | 305 (506) x 1910 x 566 | 705 (982) x 1885 x 603 | 1100 x 1900 x 750 |

* l = maximum distribution distance with specific DN diameter

VACON® NXP Liquid Cooled Enclosed drive

| AC drive type | Rated current | | | Electrical output power | | Chassis | Dimensions W x H x D W/O Cooling unit [in] |
|----------------------|-----------------------------|--------------------------|--------------------------|-----------------------------------------|-----------------------------------------|---------|--------------------------------------------|
| | Thermal I _{TH} [A] | Cont. I _L [A] | Cont. I _H [A] | Motor at I _{th} (400 VAC) [kW] | Motor at I _{th} (500 VAC) [kW] | | |
| NXP13705A5T0RWN-LIQC | 1370 | 1245 | 913 | 700 | 900 | CH64 | 2000 x 2100 x 900 |
| NXP16405A5T0RWN-LIQC | 1640 | 1491 | 1093 | 900 | 1100 | CH64 | 2000 x 2100 x 900 |

| AC drive type | Rated current | | | Electrical output power | | Chassis | Dimensions W x H x D W/O Cooling unit [in] |
|----------------------|-----------------------------|--------------------------|--------------------------|-----------------------------------------|-----------------------------------------|---------|--------------------------------------------|
| | Thermal I _{TH} [A] | Cont. I _L [A] | Cont. I _H [A] | Motor at I _{th} (525 VAC) [kW] | Motor at I _{th} (690 VAC) [kW] | | |
| NXP08206A5T0RWN-LIQC | 820 | 745 | 547 | 560 | 800 | CH64 | 2000 x 2100 x 900 |
| NXP09206A5T0RWN-LIQC | 920 | 836 | 613 | 650 | 850 | CH64 | 2000 x 2100 x 900 |
| NXP10306A5T0RWN-LIQC | 1030 | 936 | 687 | 700 | 1000 | CH64 | 2000 x 2100 x 900 |
| NXP11806A5T0RWN-LIQC | 1180 | 1073 | 787 | 800 | 1100 | CH64 | 2000 x 2100 x 900 |
| NXP13006A5T0RWN-LIQC | 1300 | 1182 | 867 | 900 | 1200 | CH64 | 2000 x 2100 x 900 |
| NXP15006A5T0RWN-LIQC | 1500 | 1364 | 1000 | 1000 | 1400 | CH64 | 2000 x 2100 x 900 |
| NXP17006A5T0RWN-LIQC | 1700 | 1545 | 1133 | 1150 | 1550 | CH64 | 2000 x 2100 x 900 |

Technical data

| | | |
|--------------------------------|--------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Mains connection | Input voltage U_{in} | NX_5: 400...500 VAC (-10%...+10%); 465...800 VDC (-0%...+0%) NX_6: 525...690 VAC (-10%...+10%); 640...1100 VDC (-0%...+0%) NX_8: 525...690 VAC (-10%...+10%); 640...1136 VDC (-0%...+0%) ¹⁾ NX_8: 525...690 VAC (-10%...+10%); 640...1200 VDC (-0%...+0%) ²⁾ |
| | Input frequency | 45...66 Hz |
| Motor connections | Output voltage | 0- U_{in} |
| | Output frequency | 0...320 Hz |
| | Output filter | VACON® liquid cooled NX_8 unit must be equipped with a output filter with an inductance of at least 0.7%. |
| Control characteristics | Control method | Frequency control U/f Open loop vector control (5-150% of base speed): speed control 0.5%, dynamic 0.3%sec, torque lin. <2%, torque rise time ~5 ms Closed loop vector control (entire speed range): speed control 0.01%, dynamic 0.2% sec, torque lin. <2%, torque rise time ~2 ms |
| | Switching frequency | NX_5: Up to and including NX_0061: 1...16 kHz; Factory default 10 kHz From NX_0072: 1...6 kHz; Factory default 3.6 kHz (1...10 kHz with special application) NX_6/NX_8: 1...6 kHz; Factory default 1.5 kHz |
| | Field weakening point | 8...320 Hz |
| | Acceleration time | 0...3000 sec |
| | Deceleration time | 0...3000 sec |
| | Braking | DC brake: 30% of TN (without brake resistor), flux braking |
| | Ambient conditions | Ambient operating temperature |
| | Installation temperature | 0...+70 °C |
| | Storage temperature | -40 °C...+70 °C; no liquid in heatsink under 0 °C |
| | Relative humidity | 5 to 96% RH, non-condensing, no dripping water |
| | Air quality - chemical vapours - mechanical particles" | No corrosive gases IEC 60721-3-3, unit in operation, class 3C2 IEC 60721-3-3, unit in operation, class 3S2 (no conductive dust allowed) |
| | Altitude | NX_5: (380...500 V): 3000 m ASL; in case network is not corner grounded NX_6/NX_8: (525...690 V) max. 2000 m ASL. For further requirements, contact factory 100% load capacity (no derating) up to 1,000 m; above 1,000 m derating of maximum ambient operating temperature by 0,5 °C per each 100 m is required. |
| | Vibration | 5...150 Hz |
| | EN50178/EN60068-2-6 | Displacement amplitude 0.25 mm (peak) at 3...31 Hz Max acceleration amplitude 1 G at 31...150 Hz |
| | Shock EN50178, EN60068-2-27 | UPS Drop Test (for applicable UPS weights) Storage and shipping: max 15 G, 11 ms (in package) |
| | Enclosure class | IP00 / standard in entire kW/HP range |
| EMC | Immunity | Fulfils all EMC immunity requirements |
| | Emissions | EMC level N, T (IT networks) |
| Safety | | EN 50178, EN 60204-1, IEC 61800-5-1, CE, UL, CUL; (see unit nameplate for more details) |
| Functional safety *) | STO | EN/IEC 61800-5-2 Safe Torque Off (STO) SIL2, EN ISO 13849-1 PL"d" Category 3, EN 62061: SILCL2, IEC 61508: SIL2. |
| | SS1 | EN /IEC 61800-5-2 Safe Stop 1 (SS1) SIL2, EN ISO 13849-1 PL"d" Category 3, EN /IEC62061: SILCL2, IEC 61508: SIL2. |
| | ATEX Thermistor input | 94/9/EC, CE 0537 Ex 11 (2) GD |
| Approvals | Type tested | SGS Fimko CE, UL |
| | Type approval | DNV, BV, Lloyd's Register (other marine societies delivery based approvals) |
| | Approvals our partners have | Ex, SIRA |
| Liquid cooling | Allowed cooling agents | Drinking water Water-glycol mixture |
| | Temperature of cooling agent | 0...35 °C (I_{th})(input); 35...55 °C, please see manual for further details Temperature rise during circulation max. 5 °C No condensation allowed |
| | System max. working pressure | 6 bar/ 30 bar peak |
| | Pressure loss (at nominal flow) | Varies according to size, please see manual for further details |
| Protections | | Overvoltage, undervoltage, earth fault, mains supervision, motor phase supervision, overcurrent, unitover-temperature, motor overload, motor stall, motor underload, short-circuit of +24 V and +10V reference voltages. |

*) with OPT-AF board (SS1 requires external safety relay)

1) NX_8 drives only available as Ch6x NXB units.

2) NX_8 drives only available as Ch6x NXA/NXP units.

Typecode key

VACON® NXP Liquid Cooled drives

| | | | | | | | | | | | | |
|-----|------|---|---|---|---|---|---|---|---|----------------|-------|-------|
| NXP | 0000 | 5 | A | 0 | N | 1 | S | W | V | A1 A2 00 00 C3 | -LIQC | +HXC1 |
|-----|------|---|---|---|---|---|---|---|---|----------------|-------|-------|

| | |
|-------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| NXP | ■ Product Range NXP = AC drive or inverter unit NXA = Active front-end unit NXB = Brake-chopper unit NXN = Non Regenerative Front End (NFE) |
| 0000 | ■ Nominal current 0007 = 7 A 0022 = 22 A 0205 = 205 A etc. |
| 5 | ■ Nominal mains voltage 5 = 380-500 VAC 6 = 525-690 VAC |
| A | ■ Control keypad A = standard alpha-numeric B = no local control keypad F = dummy panel G = graphical keypad |
| 0 | ■ Enclosure class 0 = IP00 5 = IP54 |
| N | ■ EMC emission levels N = No EMC emission protection; to be installed on enclosures T = Fulfills standard 61800-3 for IT-networks |
| 1 | ■ Brake chopper 0 = no brake chopper 1 = integrated brake chopper (CH3, CH72 (6-pulse) & CH74 only) |
| S | ■ Hardware modifications: supply I = Inverter unit; DC-supply 2 = Active front-end unit S = 6-pulse with A/C chokes N = 6-pulse, no chokes T = 12-pulse with A/C chokes U = 12-pulse, no chokes W = 12-pulse with L/C chokes R = Low harmonic |
| W | ■ Hardware modifications: cooling W = Liquid-cooled module with aluminium heatsink P = Liquid-cooled module with nickel-coated aluminium heatsink |
| V | ■ Hardware modifications: boards F = Fiber connection, standard (from CH61) G = Fiber connection, varnished (from CH61) S = Direct connection, standard V = Direct connection, varnished |
| | ■ If OPT-AF option board is used N = IP54 control box, fiber connection, standard boards, (from CH61) O = IP54 control box, fiber connection, varnished boards, (from CH61) |
| A1 | ■ Option boards; each slot is represented by two characters: A = basic I/O boards, B = expander I/O boards C = fieldbus boards D = special boards |
| A2 | |
| 00 | |
| 00 | |
| C3 | |
| -LIQC | ■ Liquid Cooled Enclosed Drive |
| +HXC1 | ■ Heat Exchanger option for enclosed drive +HXC1 = Stainless steel piping, 1-pump +HXC2 = Stainless steel piping, 2-pumps |

*) Note, the control unit of NX_8 drives need to be supplied with a external 24 Vdc power source.



Marine approvals

Type approvals



Delivery based approvals



Option boards

| Type | Card slot | | | | | I/O signal | | | | | | | | | | | | | | | | | | Note | | | | | |
|------------------------------------|-----------|---|---|---|---|------------|----|-------|-----------------|------------------|-----------|------------------|------------|---------|---------------------|-------|---------------|--------|--------|------------------|------------------|---------------|-----------|------|-----------|-------------------|-----------------------------------|-------------------------------|----------------------------------------|
| | A | B | C | D | E | DI | DO | DI DO | AI (mA/V/±V) | AI (mA) isolated | AO (mA/V) | AO (mA) isolated | RO (NO/NC) | RO (NO) | +10V _{ref} | Therm | +24V/EXT +24V | pt 100 | KTY 84 | 42-240 VAC input | DI/DO (10...24V) | DI/DO (RS422) | DI ~1Vp-p | | Re-solver | Out +5V/+15V/+24V | Out +15V/+24V | Out +5V/+12V/+15V | |
| Basic I/O cards (OPT-A) | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| OPT-A1 | ■ | | | | | 6 | 1 | | 2 | | 1 | | | | 1 | | 2 | | | | | | | | | | | | |
| OPT-A2 | ■ | | | | | | | | | | | | 2 | | | | | | | | | | | | | | | | |
| OPT-A3 | ■ | | | | | | | | | | | | 1 | 1 | | 1 | | | | | | | | | | | | | |
| OPT-A4 | | ■ | | | | 2 | | | | | | | | | | | | | | | | 3/0 | | | 1 | | | | |
| OPT-A5 | | ■ | | | | 2 | | | | | | | | | | | | | | | | 3/0 | | | | 1 | | | |
| OPT-A7 | | ■ | | | | | | | | | | | | | | | | | | | | 6/2 | | | | 1 | | 2 enc. input + 1 enc. output | |
| OPT-A8 | ■ | | | | | 6 | 1 | | 2 | | 1 | | | | 1 | | 2 | | | | | | | | | | | 1) | |
| OPT-A9 | ■ | | | | | 6 | 1 | | 2 | | 1 | | | | 1 | | 2 | | | | | | | | | | | 2.5 mm ² terminals | |
| OPT-AE | | ■ | | | | | 2 | | | | | | | | | | | | | | | 3/0 | | | | 1 | | DO = Divider + Direction | |
| OPT-AF | ■ | | | | | 2 | | | | | | | 1 | 1 | | 1 | | | | | | | | | | | | | |
| OPT-AK | | ■ | | | | | | | | | | | | | | | | | | | | | 3 | | | 1 | | Sin/Cos/ Marker | |
| OPT-AN | ■ | | | | | 6 | | | 2 | | 2 | | | | | | | | | | | | | | | | | Limited support | |
| OPT-AJ | ■ | | | | | | 1 | | 2 ³⁾ | | 1 | | | | | | 1 | | | | | | | | 1 | 1 | | | |
| I/O expander cards (OPT-B) | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| OPT-B1 | ■ | ■ | ■ | ■ | | | | 6 | | | | | | | | 1 | | | | | | | | | | | | | Selectable DI/DO |
| OPT-B2 | ■ | ■ | ■ | ■ | | | | | | | | | 1 | 1 | | 1 | | | | | | | | | | | | | |
| OPT-B4 | ■ | ■ | ■ | ■ | | | | | 1 | | 2 | | | | | | 1 | | | | | | | | | | | | 2) |
| OPT-B5 | ■ | ■ | ■ | ■ | | | | | | | | | | | | | | | | | | | | | | | | | |
| OPT-B8 | ■ | ■ | ■ | ■ | | | | | | | | | | | | | 1 | 3 | | | | | | | | | | | |
| OPT-B9 | ■ | ■ | ■ | ■ | | 2 | | | | | | | | | 1 | | | | | | | | | | | | | | |
| OPT-BH | ■ | ■ | ■ | ■ | | | | | | | | | | | | | | 3 | 3 | | | | | | | | | 3 x pt1000; 3 x Ni1000 | |
| OPT-BB | ■ | | | | | 2 | | | | | | | | | | | | | | | | | 0/2 | 2 | | | 1 | Sin/Cos + EnDat | |
| OPT-BC | ■ | | | | | | | | | | | | | | | | | | | | | 3/3 | | 1 | | | Encoder out = Resolver simulation | | |
| OPT-BE | ■ | ■ | ■ | ■ | | | | | | | | | | | | | | | | | | | | | | | | EnDat/SSI | |
| Fieldbus cards (OPT-C) | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| OPT-C2 | | ■ | ■ | | | | | | | | | | | | | | | | | | | | | | | | | | Modbus, N2 |
| OPT-C3 | | ■ | ■ | | | | | | | | | | | | | | | | | | | | | | | | | | |
| OPT-C4 | | ■ | ■ | | | | | | | | | | | | | | | | | | | | | | | | | | |
| OPT-C5 | | ■ | ■ | | | | | | | | | | | | | | | | | | | | | | | | | | |
| OPT-C6 | | ■ | ■ | | | | | | | | | | | | | | | | | | | | | | | | | | |
| OPT-C7 | | ■ | ■ | | | | | | | | | | | | | | | | | | | | | | | | | | |
| OPT-C8 | | ■ | ■ | | | | | | | | | | | | | | | | | | | | | | | | | | Modbus, N2 |
| OPT-CG | | ■ | ■ | | | | | | | | | | | | | | | | | | | | | | | | | | |
| OPT-CJ | | ■ | ■ | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Communication cards (OPT-D) | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| OPT-D1 | | ■ | ■ | | | | | | | | | | | | | | | | | | | | | | | | | | |
| OPT-D2 | | ■ | ■ | | | | | | | | | | | | | | | | | | | | | | | | | | |
| OPT-D3 | | ■ | ■ | | | | | | | | | | | | | | | | | | | | | | | | | | |
| OPT-D6 | ■ | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| OPT-D7 | ■ | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Fieldbus Cards (OPT-E) | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| OPT-E9 | | ■ | ■ | | | | | | | | | | | | | | | | | | | | | | | | | | PROFINET I/O, EtherNet/IP™, Modbus TCP |
| OPT-EC | | ■ | ■ | | | | | | | | | | | | | | | | | | | | | | | | | | |

1) Analogue signals galvanically isolated as a group
 2) Analogue signals galvanically isolated separately
 3) Only voltage input



A better tomorrow is **driven by drives**

Danfoss Drives is a world leader in variable speed control of electric motors.

We offer you unparalleled competitive edge through quality, application-optimized products and a comprehensive range of product lifecycle services.

You can rely on us to share your goals. Striving for the best possible performance in your applications is our focus. We achieve this by providing the innovative products and application know-how required to optimize efficiency, enhance usability, and reduce complexity.

From supplying individual drive components to planning and delivering complete drive systems; our experts are ready to support you all the way.

You will find it easy to do business with us. Online, and locally in more than 50 countries, our experts are never far away, reacting fast when you need them.

You gain the benefit of decades of experience, since 1968. Our low voltage and medium voltage AC drives are used with all major motor brands and technologies in power sizes from small to large.

VACON® drives combine innovation and high durability for the sustainable industries of tomorrow.

For long lifetime, top performance, and full-throttle process throughput, equip your demanding process industries and marine applications with VACON® single or system drives.

- n Marine and Offshore
- n Oil and Gas
- n Metals
- n Mining and Minerals
- n Pulp and Paper

- n Energy
- n Elevators and Escalators
- n Chemical
- n Other heavy-duty industries

VLT® drives play a key role in rapid urbanization through an uninterrupted cold chain, fresh food supply, building comfort, clean water and environmental protection.

Outmaneuvering other precision drives, they excel, with remarkable fit, functionality and diverse connectivity.

- n Food and Beverage
- n Water and Wastewater
- n HVAC
- n Refrigeration
- n Material Handling
- n Textile

VLT® | VAGON®

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without subsequential changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.